

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0745460801

Status:

Active

Overview:

[iPass Connector System](#)

Description:

iPass PCIe x8 Cable Assembly, 28 AWG, 1.0m Length

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR64395
UL	E72548
General	
Product Family	Cable Assemblies
Series	74546
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PCI Express-to-PCI Express
Overview	iPass Connector System
Product Name	iPass, PCI Express
Taxonomy	High-Speed Pluggable I/O Cable
UPC	822350025829
Physical	
Cable Length	1.0m
Circuits (Loaded)	68
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Net Weight	315.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Single Ended	No
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round
Electrical	
Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-74546-800-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Contained Per -	
D(2022)4187-DC (10	
June 2022)	
C,C'-	
azodi(formamide)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[74546](#) Series

Mates With

[75586](#) iPass Receptacle

Use With

[74540](#) PCIe Guide Frame

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION