

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010448](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Crimp Terminal Insert, Male, 12-Pole, 10A, Size 3A «21x21»](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	3A «21x21»
Component Type	Inserts - Crimp Contact
Insert Series	S-Q12/0
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
Taxonomy	Heavy-Duty Connectors
UPC	887191891064
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	11.600/g
Number of Rows	4
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	12
Temperature Range - Operating	-40° to +125°C
Tightening Test Torque	0.25 Nm
Electrical	
Current - Maximum per Contact	10.0A
Voltage - Maximum	400V
Material Info	
Engineering Number	7612.5905.0



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)10043-DC (17 Jan 2022) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates ZZCERT_CE - Declaration of Conformity
	Green Image Not Relevant Not Contained CER_4000432592_00_000.pdf

Search Parts in this Series
[93601](#) Series

Mates With
[936010447](#) Female Screw Axial Terminal
Insert

Use With
Size 3A «21x21» Hoods and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION