

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010690

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, Size 3A «21x21», M20 Thread, Grey White



Series image - Reference only

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	IP67 with screw gasket.
Component Size	3A «21x21»
Component Type	Single Lever Coupler
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Taxonomy	Heavy-Duty Connectors
Type	STD
UPC	887191842776
Physical	
Entry Location	Top
Flammability	UL 94V-0
Hood Color	Grey White RAL 9002
Lock to Mating Part	Yes
Material - Hood	Polyamide
Material - Lever	Polyamide
Net Weight	15.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	230V / 400V
Material Info	
Engineering Number	7803.6231.0
Reference - Drawing Numbers	
Sales Drawing	936010690-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000432592_00_000.pdf

Declaration of

Conformity

Search Parts in this Series

93601 Series

Use With

Size 3A «21x21» S-A, S-D, and S-Q Inserts