

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300250294

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, Gray DeviceNet Thin (Drop) Cable, 4.0m (13.12') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR6837
UL	E152210

General

Product Family	Industrial Cordsets
Series	130025
Connector End A	Mini-Change
Connector End B	Mini-Change
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Mini-Change Connectors
Product Name	DeviceNet Trunk, Mini-Change
Region	Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78678829133

Physical

Cable Diameter	7.24mm (.285")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Coupling Nut	Die-Cast Zinc
Material - Plating Mating	Gold
Net Weight	364.421/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire Size AWG	22
Wire/Cable Type	Thin (Drop)

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC

Material Info

Engineering Number	DND11A-M040
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	SD-130025-019-001
---------------	-------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000408918_00_000.pdf
ZZCERT_UKCA - Declaration of Conformity	CER_4000410285_00_000.pdf

Search Parts in this Series

130025 Series

This document was generated on 11/28/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION