






Part No.	X = Body Length
PLP5-2-100-D	0.100 (2.5mm)
PLP5-2-125-D	0.125 (3.2mm)
PLP5-2-2.5MM-D	2.5mm (0.100")
PLP5-2-3MM-D	3mm (0.118")

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	07/15/15	J. C.



2. MATERIAL: POLYCARBONATE, 94V-0, WHITE DIFFUSED.
1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101 and BSMC-1001.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974		
<u>DECIMALS</u>	<u>ANGULAR</u>			
.X ± .1	X° ± 1°		TITLE: PRESS-FIT PANEL MOUNT, 5mm LIGHT PIPE, FRONT MOUNT, DIFFUSED	
.XX ± .01				
.XXX ± .005				
DESIGNED: Brian Oliver	DATE: 04/02/15	PART NO: PLP5-2-XXX-D		
CHECKED: A. Wright	DATE: 04/02/15	CAGE CODE : 32559 SHEET # 1 OF 1		
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.				