

TiN Bits

TiN (>90 HRC)
SX 75 (>60 HRC)



021
C 6,3
TiN



TiN Bit C 6,3 Pozidriv

TiN Bit C 6,3 Pozidriv



PZ				Art.-Nr.		EAN-Code	
1	25 mm	C 6,3	1/4"	10	021 010 70	5	40 07157 10313 0
1 (VE 100)	25 mm	C 6,3	1/4"	100	021 010 77	500	40 07157 53415 6
2	25 mm	C 6,3	1/4"	10	021 020 70	5	40 07157 10314 7
2 (VE 100)	25 mm	C 6,3	1/4"	100	021 020 76	500	40 07157 53417 0
3	25 mm	C 6,3	1/4"	10	021 030 70	5	40 07157 10315 4
3 (VE 100)	25 mm	C 6,3	1/4"	100	021 030 77	500	40 07157 53419 4

022
C 6,3
TiN



TiN Bit C 6,3 Phillips

TiN Bit C 6,3 Phillips



PH				Art.-Nr.		EAN-Code	
1	25 mm	C 6,3	1/4"	10	022 010 70	5	40 07157 10316 1
1 (VE 100)	25 mm	C 6,3	1/4"	100	022 010 77	500	40 07157 53421 7
2	25 mm	C 6,3	1/4"	10	022 020 70	5	40 07157 10317 8
2 (VE 100)	25 mm	C 6,3	1/4"	100	022 020 77	500	40 07157 52339 6
3	25 mm	C 6,3	1/4"	10	022 030 70	5	40 07157 10318 5
3 (VE 100)	25 mm	C 6,3	1/4"	100	022 030 77	500	40 07157 53423 1

022
C 6,3
TiN



TiN Bit C 6,3 Phillips „Grabber“

TiN Bit C 6,3 Phillips "Grabber"



extra slim



PH				Art.-Nr.		EAN-Code	
2	25 mm	C 6,3	1/4"	10	022 002 70	5	40 07157 52471 3