

024 C 6,3



Industrie Bit C 6,3 Sechskant
Industrial Bit C 6,3 Hexagon



mm				Art.-Nr.		EAN-Code
2	25 mm	C 6,3 1/4"	10	024 200 10	5	40 07157 30952 5
2,5	25 mm	C 6,3 1/4"	10	024 250 10	5	40 07157 30253 3
3	25 mm	C 6,3 1/4"	10	024 300 10	5	40 07157 30255 7
4	25 mm	C 6,3 1/4"	10	024 400 10	5	40 07157 30257 1
5	25 mm	C 6,3 1/4"	10	024 500 10	6	40 07157 30259 5
5,5	25 mm	C 6,3 1/4"	10	024 550 10	6	40 07157 62319 5
6	25 mm	C 6,3 1/4"	10	024 600 10	7	40 07157 30261 8
8	25 mm	C 6,3 1/4"	10	024 800 10	9	40 07157 30263 2
3/32"	25 mm	C 6,3 1/4"	10	024 238 10	8	40 07157 64871 6
3/16"	25 mm	C 6,3 1/4"	10	024 476 20	8	40 07157 64873 0
1/4"	25 mm	C 6,3 1/4"	10	024 635 20	8	40 07157 64875 4

025 C 6,3



Industrie Bit C 6,3 Square
Industrial Bit C 6,3 Square



SQ				Art.-Nr.		EAN-Code
0 (1,75 mm)	25 mm	C 6,3 1/4"	10	025 000 10	4	40 07157 50350 3
1 (2,30 mm)	25 mm	C 6,3 1/4"	10	025 100 10	4	40 07157 50352 7
2 (2,80 mm)	25 mm	C 6,3 1/4"	10	025 200 10	5	40 07157 50354 1
3 (3,30 mm)	25 mm	C 6,3 1/4"	10	025 300 10	5	40 07157 50356 5

026 C 6,3



Industrie Bit C 6,3 TORX®
Industrial Bit C 6,3 TORX®



Torx®				Art.-Nr.		EAN-Code
5	25 mm	C 6,3 1/4"	10	026 050 10	4	40 07157 50779 2
6	25 mm	C 6,3 1/4"	10	026 060 10	4	40 07157 30953 2
7	25 mm	C 6,3 1/4"	10	026 070 10	4	40 07157 30954 9
8	25 mm	C 6,3 1/4"	10	026 080 10	4	40 07157 30955 6
9	25 mm	C 6,3 1/4"	10	026 090 10	4	40 07157 30956 3
10	25 mm	C 6,3 1/4"	10	026 100 10	5	40 07157 30957 0
10 (VE 100)	25 mm	C 6,3 1/4"	100	026 100 17	460	40 07157 31561 8
15	25 mm	C 6,3 1/4"	10	026 150 10	5	40 07157 30959 4
15 (VE 100)	25 mm	C 6,3 1/4"	100	026 150 17	480	40 07157 31563 2
20	25 mm	C 6,3 1/4"	10	026 200 10	5	40 07157 30961 7
20 (VE 100)	25 mm	C 6,3 1/4"	100	026 200 17	510	40 07157 31565 6
25	25 mm	C 6,3 1/4"	10	026 250 10	5	40 07157 30963 1
25 (VE 100)	25 mm	C 6,3 1/4"	100	026 250 17	530	40 07157 31567 0
27	25 mm	C 6,3 1/4"	10	026 270 10	5	40 07157 30965 5
30	25 mm	C 6,3 1/4"	10	026 300 10	6	40 07157 30967 9
30 (VE 100)	25 mm	C 6,3 1/4"	100	026 300 17	620	40 07157 31569 4
40	25 mm	C 6,3 1/4"	10	026 400 10	6	40 07157 30969 3
40 (VE 100)	25 mm	C 6,3 1/4"	100	026 400 17	620	40 07157 31571 7
45	25 mm	C 6,3 1/4"	10	026 450 10	7	40 07157 32076 6
50	26 mm	C 6,3 1/4"	10	026 500 10	8	40 07157 32450 4
50	32 mm	C 6,3 1/4"	10	026 501 10	10	40 07157 51399 1