


**039
E 6,3**


**Steckschlüsselbit
E 6,3 metrisch mit Magnet**
*Socket Bit E 6,3 metric
with magnet*



mm		E 6,3			Art.-Nr.		EAN-Code
5	66 mm	E 6,3	1/4"	5	039 050 10	28	40 07157 50404 3
6	66 mm	E 6,3	1/4"	5	039 060 10	27	40 07157 50406 7
7	66 mm	E 6,3	1/4"	5	039 070 10	26	40 07157 51373 1
8	66 mm	E 6,3	1/4"	5	039 080 10	31	40 07157 50408 1
9	66 mm	E 6,3	1/4"	5	039 090 10	33	40 07157 53245 9
10	66 mm	E 6,3	1/4"	5	039 100 10	36	40 07157 50410 4
11	66 mm	E 6,3	1/4"	5	039 110 10	36	40 07157 53247 3
12	66 mm	E 6,3	1/4"	5	039 120 10	39	40 07157 53249 7
13	66 mm	E 6,3	1/4"	5	039 130 10	54	40 07157 50412 8

**039
E 6,3**

**Steckschlüsselbit
E 6,3 Inch mit Magnet**
*Socket Bit E 6,3 Inch
with magnet*



		E 6,3			Art.-Nr.		EAN-Code
5/16"	66 mm	E 6,3	1/4"	5	039 516 10	31	40 07157 50414 2
3/8"	66 mm	E 6,3	1/4"	5	039 038 10	36	40 07157 50416 6

**039
E 6,3**

**Steckschlüsselbitsatz
E 6,3 metrisch mit Magnet**
*Socket Bitset E 6,3 metric
with magnet*



			Art.-Nr.		EAN-Code
6 / 7 / 8 / 10 / 12 / 13 mm			039 961 06	550	40 07157 63841

Spezial Bits für direkten Maschinenanschluss

Special Bits for direct fit

 A5,5 AEG BOSC HOLZ-HER KRESS METABO	 G7 BAIER FEIN	 C8 BOSCH FEIN HOLZ-HER LECUREUX METABO	 M5 BÖLLHOFF/ UNIQUE HOLZ-HER WEBER	 10/32" NFA USM DUOFAST DVSG
--	--	---	---	--