

061

6,3 mm



Industrie Umsteckbit 1/4" Pozidriv

Industrial Reversible Bit 1/4" Pozidriv



PZ	Length	Shank	Box	Art.-Nr.	U	EAN-Code
1/2	60 mm	1/4"	10	061 126 10	13	40 07157 30429 2
2/2	60 mm	1/4"	10	061 226 10	13	40 07157 50522 4
2/3	60 mm	1/4"	10	061 236 10	14	40 07157 30431 5

062

6,3 mm



Industrie Umsteckbit 1/4" Phillips

Industrial Reversible Bit 1/4" Phillips



PH	Length	Shank	Box	Art.-Nr.	U	EAN-Code
1/2	60 mm	1/4"	10	062 126 10	12	40 07157 30433 9
2/2	60 mm	1/4"	10	062 226 10	13	40 07157 50524 8
2/3	60 mm	1/4"	10	062 236 10	13	40 07157 30435 3

063

6,3 mm



Industrie Umsteckbit 1/4" Phillips/Schlitz

Industrial Reversible Bit 1/4" Phillips/Slotted



PH	Length	Shank	Box	Art.-Nr.	U	EAN-Code
5,5 PH2	60 mm	1/4"	10	063 255 10	12	40 07157 32556 3

070

C 8



Industrie Bit C 8 Schlitz

Industrial Bit C 8 Slotted



					Art.-Nr.		EAN-Code
5,5 x 0,8	32 mm	C 8	5/16"	10	070 514 10	8	40 07157 30988 4
5,5 x 1,0	32 mm	C 8	5/16"	10	070 524 10	8	40 07157 30989 1
6,0 x 1,0	32 mm	C 8	5/16"	10	070 604 10	9	40 07157 30990 7
6,5 x 1,2	32 mm	C 8	5/16"	10	070 614 10	9	40 07157 30991 4
8,0 x 1,2	32 mm	C 8	5/16"	10	070 804 10	11	40 07157 30992 1
8,0 x 1,6	32 mm	C 8	5/16"	10	070 814 10	11	40 07157 30993 8
10,0 x 1,6	38 mm	C 8	5/16"	10	070 104 10	17	40 07157 30986 0
12,0 x 2,0	38 mm	C 8	5/16"	10	070 204 10	21	40 07157 30987 7

071

C 8



Industrie Bit C 8 Pozidriv

Industrial Bit C 8 Pozidriv



PZ					Art.-Nr.		EAN-Code
1	32 mm	C 8	5/16"	10	071 010 10	9	40 07157 30994 5
2	32 mm	C 8	5/16"	10	071 020 10	10	40 07157 30995 2
3	32 mm	C 8	5/16"	10	071 030 10	11	40 07157 30996 9
4	38 mm	C 8	5/16"	10	071 042 10	17	40 07157 30997 6