

400



ERGONIC® - Schlitz-Schraubendreher mit 3K-Griff

ERGONIC® - Slotted-Screwdriver with 3C-handle



							Art.-Nr.		EAN-Code
2,5 x 0,4 EI	75	86	25	2,50	12		400 022 10	27	40 07157 53679 2
3,0 x 0,5 EI	80	86	25	3,00	12		400 032 10	30	400 7157 53117 9
3,5 x 0,6 EI	100	86	25	3,50	12		400 353 10	33	400 7157 53119 3
4,0 x 0,8 EI	100	94	30	4,00	12		400 043 10	49	400 7157 53611 2
4,0 x 0,8 EI	200	94	30	4,00	6		400 047 10	58	400 7157 50693 1
4,0 x 0,8 EI	300	94	30	4,00	3		400 049 10	68	400 7157 51379 3
5,0 x 0,8	150	101	33	5,00	12		400 055 10	75	400 7157 53619 8
5,5 x 1,0	125	101	33	5,00	12		400 554 10	72	400 7157 53621 1
5,5 x 1,0 EI	150	101	33	5,00	12		400 555 10	82	400 7157 53623 5
5,5 x 1,0 EI	200	101	33	5,00	6		400 557 10	92	400 7157 53697 6
5,5 x 1,0 EI	300	101	33	5,00	3		400 559 10	111	400 7157 50695 5
6,0 x 1,2	100	106	36	6,00	12		400 063 10	79	400 7157 57589 0
6,0 x 1,2	150	106	36	6,00	12		400 065 10	99	400 7157 57591 3
6,0 x 1,2	200	106	36	6,00	12		400 067 10	112	400 7157 57593 7
6,5 x 1,2	100	106	36	6,00	12		400 653 10	79	400 7157 53627 3
6,5 x 1,2	150	106	36	6,00	12		400 655 10	102	400 7157 52799 8
6,5 x 1,2	200	106	36	6,00	12		400 657 10	112	400 7157 53629 7
6,5 x 1,2	500	106	36	6,00	3		400 610 10	190	400 7157 53699 0
8,0 x 1,2	175	112	39	7,00	12		400 086 10	135	400 7157 52801 8
8,0 x 1,2 EI	300	112	39	8,00	3		400 088 10	198	400 7157 51809 5
10,0 x 1,6	200	112	39	8,00	6		400 107 10	162	400 7157 53681 5

EI = Elektriker Klinge / EI = electrician blade

401



ERGONIC® - Pozidriv-Schraubendreher mit 3K-Griff

ERGONIC® - Pozidriv-Screwdriver with 3C-handle



PZ						Art.-Nr.		EAN-Code
0	60	86	25	3,00	6	401 001 10	30	40 07157 22100 1
1	80	94	30	4,50	12	401 102 10	50	40 07157 53683 9
2	100	106	36	6,00	12	401 203 10	92	40 07157 53685 3
2	300	106	36	6,00	3	401 209 10	125	40 07157 51769 2
3	150	112	39	8,00	6	401 305 10	148	40 07157 53687 7
4	150	112	39	10,00	6	411 405 40*	228	40 07157 64355 1

*Sechskant-Klinge / Hex-Blade