

402



ERGONIC® - Phillips-Schraubendreher mit 3K-Griff

ERGONIC® - Phillips-Screwdriver with 3C-handle



PH				Ø		Art.-Nr.		EAN-Code
0	60	86	25	3,00	6	402 001 10	30	40 07157 22106 3
1	80	94	30	4,50	12	402 102 10	50	40 07157 52803 2
1	200	94	30	4,50	3	402 107 10	65	40 07157 22111 7
2	100	106	36	6,00	12	402 203 10	92	40 07157 52805 6
2	150	106	36	6,00	12	402 205 10	103	40 07157 53637 2
2	200	106	36	6,00	6	402 207 10	114	40 07157 53639 6
2	300	106	36	6,00	3	402 209 10	123	40 07157 51381 6
2	500	106	36	6,00	3	402 210 10	187	40 07157 57813 6
3	150	112	39	8,00	6	402 305 10	146	40 07157 53689 1
4	150	112	39	10,00	6	412 405 40*	228	40 0715763079 7

*Sechskant-Klinge/Hex-Blade

404



ERGONIC® - Square-Schraubendreher mit 3K-Griff

ERGONIC® - Square-Screwdriver with 3C-handle



SQ				Ø		Art.-Nr.		EAN-Code
0 (1,75 mm)	100	94	30	3,0	12	404 000 40	44	40 07157 60309 8
1 (2,30 mm)	120	94	30	4,5	12	404 100 40	56	40 07157 53507 8
2 (2,80 mm)	160	106	36	5,0	12	404 200 40	91	40 07157 53509 2
3 (3,30 mm)	160	106	36	6,0	12	404 300 40	105	40 07157 53511 5

408



ERGONIC® - TORX®-Schraubendreher mit 3K-Griff

ERGONIC® - TORX®-Screwdriver with 3C-handle



Torx®				Ø		Art.-Nr.		EAN-Code
5	60	86	25	3,0	6	408 051 40	20	40 07157 22188 9
6	60	86	25	3,0	6	408 061 40	20	40 07157 22154 4
7	60	86	25	3,0	12	408 071 40	28	40 07157 52807 0
8	60	86	25	3,0	12	408 083 40	28	40 07157 52809 4
9	60	86	25	3,5	12	408 093 40	28	40 07157 52811 7
10	100	86	25	3,5	12	408 103 40	33	40 07157 52813 1
15	100	94	30	4,0	12	408 153 40	50	40 07157 52815 5
20	100	101	33	5,0	12	408 203 40	68	40 07157 52817 9
25	100	106	36	5,0	12	408 253 40	82	40 07157 52819 3
27	100	106	36	5,0	12	408 273 40	82	40 07157 52821 6
30	115	112	39	6,0	6	408 303 40	103	40 07157 52823 0
40	125	112	39	8,0	6	408 404 40	136	40 07157 52825 4
45	125	112	39	8,0	3	408 454 40	130	40 07157 22166 7