

413



ERGONIC® VDE E-slim - Schlitz-Schraubendreher mit 3K-Griff

ERGONIC® VDE E-slim - Slotted-Screwdriver with 3C-handle



1000 V
IEC 60900:2018

							Art.-Nr.		EAN-Code
3,0 x 0,5	100	105	25	3,5	12		413 930 90	45	40 07157 62631 8
3,5 x 0,6	100	105	25	3,5	12		413 935 90	45	40 07157 62635 6
3,5 x 0,8	100	105	25	3,5	12		413 938 90	45	40 07157 62637 0
4,0 x 0,8	100	105	25	4,0	12		413 940 90	46	40 07157 62639 4
4,5 x 1,0	125	115	27	4,5	12		413 945 90	62	40 07157 62641 7
5,5 x 1,0	125	115	27	5,5	12		413 955 90	73	40 07157 62643 1
6,5 x 1,2	125	115	27	6,5	12		413 965 90	86	40 07157 62645 5

414



ERGONIC® VDE E-slim - Phillips-Schraubendreher mit 3K-Griff

ERGONIC® VDE E-slim - Phillips-Screwdriver with 3C-handle



1000 V
IEC 60900:2018

PH							Art.-Nr.		EAN-Code
1	80	105	25	4,5	12		414 192 90	45	40 07157 62647 9
2	100	115	27	6,0	12		414 293 90	73	40 07157 62649 3

415



ERGONIC® VDE E-slim - Pozidriv-Schraubendreher mit 3K-Griff

ERGONIC® VDE E-slim - Pozidriv-Screwdriver with 3C-handle



1000 V
IEC 60900:2018

PZ							Art.-Nr.		EAN-Code
1	80	105	25	4,5	12		415 192 90	44	40 07157 62651 6
2	100	115	27	6,0	12		415 293 90	73	40 07157 62653 0

416



ERGONIC® VDE E-slim - (+/-) H-Schraubendreher mit 3K-Griff

ERGONIC® VDE E-slim - (+/-) H-Screwdriver with 3C-handle



1000 V
IEC 60900:2018

PlusMinus							Art.-Nr.		EAN-Code
H 1	80	105	25	4,5	12		416 192 90	45	40 07157 62655 4
H 2	100	115	27	6,0	12		416 293 90	73	40 07157 62657 8