

USB Type-C 6-in-1 multi-port adapter (Hub3.1 + HDMI + VGA + PD + card reader + stereo audio), space grey

A-CM-COMBO6-01

- 6-in-1: USB3 port, 4K HDMI and Full HD VGA video, stereo audio, card reader and USB Type-C PD charge support
- Practical card reader, video and audio outputs
- Plug & Play



Features

- USB 3.1 Gen 1 (5 Gbps) port
- HDMI port with UHD 4K @30 Hz support
- VGA Full HD video port
- Audio stereo 3.5 mm output
- 60 W USB Type-C Power Delivery 3.0 port
- SD and MicroSD card reader/writer
- Durable premium style metal housing

Specifications

Input: USB 3.x Type-C male; 15 cm cable length
USB 3.1 Gen 1 output (5 Gbps): 1 pcs x Type-A (female, blue)

HDMI output: Type-A (female), max. resolution: 4K @ 30 Hz
USB Type-C PD port: Max. PD 2.0 up to 60 W
SD card-reader: SD and MicroSD formats, supports cards up to 128 GB
VGA 1920 x 1080 @60 Hz video and 3.5 mm stereo audio sockets

Power consumption: 5 V DC, up to 0.2 A

Dimensions: 89 x 55 x 15 mm

Packaging

Q'ty in crtn, pcs	100
Crtn volume, CUM	0.056
Crtn weight, kgs	11.78
Individual package size LxWxH:	150x90x21 mm
Carton size LxWxH:	580x330x290 mm
Country of origin	CN
Barcode	8716309121453
Customs code	8544429090

System requirements

The USB Type-C video source device must support DisplayPort™ Alt Mode

Certificates

