

USB Type-C 9-in-1 multi-port adapter (USB hub + HDMI + VGA + PD + card reader + LAN + 3.5 mm audio), space grey

A-CM-COMBO9-01

- All functions you need in one single adapter.
- 9-in-1 functions: USB hub, 4K HDMI and Full HD VGA video, stereo audio, Gigabit LAN port, card reader and USB Type-C PD charge support
- Plug & Play



Features

- 3-port USB 3.1 Gen 1 (5 Gbps) hub
- 2-port USB 2 (480 Mbps) hub
- HDMI port with UHD 4K @30 Hz support
- VGA Full HD video port
- 3.5 mm stereo audio output
- 10/100/1000 Mbps Gigabit LAN port
- SD and Micro-SD card reader/writer
- 60 W USB Type-C Power Delivery 3.0 port
- Durable premium style metal housing

Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.026
Crtn weight, kgs	7.5
Individual package size LxWxH:	340x120x21 mm
Carton size LxWxH:	500x385x135 mm
Country of origin	CN
Barcode	8716309121439
Customs code	8544429090

Specifications

Input: USB 3.x Type-C male; 15 cm cable length
 USB 2.0 output: 2 pcs x Type-A (female)
 USB 3.1 Gen 1 output (5 Gbps): 3 pcs x Type-A (female, blue)
 HDMI output: Type-A (female), max. resolution: 4K @ 30 Hz
 USB Type-C PD port: Max. PD 2.0 up to 60 W
 LAN: Gigabit, RJ45 port
 SD card-reader: SD and MicroSD formats, supports cards up to 128 GB
 VGA 1920 x 1080 @60 Hz video and 3.5 mm stereo audio sockets

Power consumption: 5 V DC, up to 0.2 A
 Dimensions: 272 x 80 x 18 mm

System requirements

The USB Type-C video source device must support DisplayPort™ Alt Mode

Certificates

