

UPS with USB and LCD display, 3000 VA, black

EG-UPS-036

ULTIMATE DEFENCE

- Informative LCD display
- Provides backup power prevents data loss
- Protects your sensitive and valuable equipment
- Compact and reliable ideal for home and small office use



Features

- Uninterruptable 3000 VA power supply for PC's
- Automatic output voltage regulation (AVR)
- USB interface
- LCD status indication
- Short circuit protection
- Surge, spike and lightning protection
- Audible and visual alarms
- Overcharge and overdischarge protection
- Including practical UPS Management software

Packaging

Q'ty in crtn, pcs	1
Crtn volume, CUM	0.0396
Crtn weight, kgs	20.82
Individual package size LxWxH:	500x300x150 mm
Carton size LxWxH:	550x240x300 mm
Country of origin	CN
Barcode	8716309124744
Customs code	8504408590

Package contents

UPS
Power cord
USB cable
Software CD
Spare fuse

Specifications

Type: line interactive
Waveform: sine wave (AC mains), modified (square) sine wave (battery)
Input: 220 V AC $\pm$ 25% (162-295V), 50 / 60 Hz $\pm$ 10%
Output: 220 V AC $\pm$ 10%, 50 / 60 Hz $\pm$ 1% (220 V AC $\pm$ 10 % at inverter mode)
Switching time: less than 10 ms
Backup time: 8...20 mins (depends on the load)
Battery: sealed lead-acid 12 V DC / 7 Ah x 4 pcs
Charge time: up to 90% after 6-8 hours
Sockets: 1 x C14 input, 3 pcs x C13 output, 3 pcs x german Shuko output
Interface communication: USB-BF socket, RI45

System requirements

Software is compatible with Windows 7/8/10/11, Windows 2008 server

In order to work correctly, the connected load should be at least 5% of the maximum capacity of the UPS. For example, a 700 W UPS needs at least a connected load of 35 W to work

Certificates

