

Online UPS, 1000 VA

EG-UPSO-1000

ULTIMATE DEFENCE

- Protects important data from power cuts
- Protects valuable equipment
- Protects users



Features

- Online type UPS: double voltage conversion without switching the power
- USB control interface
- LCD display
- Short circuit protection
- Compatible with power generators of any brand
- Surge, spike and lightning protection
- Audible and visual alarms
- Overcharge and overdischarge protection

Packaging

Q'ty in crtn, pcs	1
Crtn volume, CUM	0.0320256
Crtn weight, kgs	10.6
Individual package size LxWxH:	400x240x320 mm
Carton size LxWxH:	417x240x320 mm
Country of origin	CN
Barcode	8716309124836
Customs code	8504408590

Package contents

UPS
Power cord
USB cable
Software CD
Spare fuse

Specifications

UPS type: online, pure sine wave
Input: 220V AC $\pm 25\%$, 50Hz / 60Hz $\pm 10\%$
Output: 220V AC $\pm 1\%$, 50Hz / 60Hz $\pm 0.5\%$ (on battery)
Output power factor: > 0.99
Inverter output efficiency (resistive load): 85%, any load type is allowed
Switching time: zero
Backup time: 8...20 mins (depends on the load)
Battery: 151 x 65 x 95 mm, sealed lead-acid 12 V / 9 Ah / 2.35 kg x 2 pcs, 24VDC
Charge time: 90% capacity restored in 3 hours
External battery connectors: yes

System requirements

In order to work correctly, the connected load should be at least 5% of the maximum capacity of the UPS. For example, a 700 W UPS needs at least a connected load of 35 W to work.

Certificates

