

Online UPS, 10000 VA, USB + SNMP slot, terminals without cables

EG-UPSO-10000

ULTIMATE DEFENCE

- Pure sine wave output
- Provide backup power Prevents data loss
- Protects your sensitive and valuable equipment
- Perfect support for solar panel installations and other sensitive equipment that requires pure sinewave input
- Compact and reliable ideal for home and small office use



Features

- Online type UPS: double voltage conversion with pure sine wave output without switching the power
- USB interface
- Automatic AC voltage regulation (AVR)
- Intelligent overloadand short-circuit protection
- Audible and visual alarms
- LCD display and LED status indication
- Internal battery with overcharge and over-discharge protection

Packaging

Q'ty in crtn, pcs	1
Crtn volume, CUM	0.16988
Crtn weight, kgs	70
Individual package size LxWxH:	685x310x800 mm
Carton size LxWxH:	685x310x800 mm
Country of origin	CN
Barcode	8716309124850
Customs code	8504408590

Package contents

UPS without cords

Specifications

Type: online
 Waveform: sine, <2% distortion at linear load (<5% non-linear), PF > 0.99
 Input: AC 176 ~ 288 V, 40 70 Hz autodetect
 Output: AC 208 V / 220 V / 230 V / 240 V (settable) ±1%, 45Hz/65Hz autosense
 Switching time: near 0 ms
 Backup time: 30 mins (depends on the load)
 Battery: UPS with sealed lead-acid 12V/9Ah 16 pcs; 192 V DC

Charge time: 90% capacity restored in 8 hours
 Input Sockets: Terminal block input Single-phase three-wire (1F + N + PE);

System requirements

In order to work correctly, the connected load should be at least 5% of the maximum capacity of the UPS. For example, a 700 W UPS needs at least a connected load of 35 W to work.

Certificates

