

Rack 2000VA UPS

UPS-RACK-2000

ULTIMATE DEFENCE

- Protects important data from power cuts
- Protects valuable equipment
- Protects users



Features

- Automatic output voltage regulation (AVR)
- Rack 3.4U metal case
- USB control interface
- LCD display
- Short circuit protection
- Compatible with power generators of any brand
- Surge, spike and lightning protection
- Audible and visual alarms
- Overcharge and overdischarge protection

Packaging

Q'ty in crtn, pcs	1
Crtn volume, CUM	0.04922
Crtn weight, kgs	16.41
Individual package size LxWxH:	535x400x230 mm
Carton size LxWxH:	535x400x230 mm
Country of origin	CN
Barcode	8716309124768
Customs code	8504408590

Package contents

UPS
Power cord
USB cable
Software CD
Spare fuse

Specifications

UPS type: line interactive
Input: 220V AC $\pm$ 25%, 50Hz / 60Hz $\pm$ 10%
Output: 220V AC $\pm$ 10%, 50Hz / 60Hz $\pm$ 0.5% (on battery)
Switching time: no more than 10 ms (typically 6 ms)
Backup time: 8...20 mins (depends on the load)
Battery: 151 x 65 x 95 mm, sealed lead-acid 12 V / 9 Ah / 2.5 kg x 2 pcs
Charge time: up to 12 hours
Sockets: IEC13 output x 2 pcs, german Shuko x 2 pcs; input IEC14, USB-BF control interface, telephone input\output
Operating conditions: 0°C~40°C, at humidity 10~90%RH non condensing
Noise: < 45 dB (at 1 meter distance)

System requirements

In order to work correctly, the connected load should be at least 5% of the maximum capacity of the UPS. For example, a 700 W UPS needs at least a connected load of 35 W to work.

Certificates

