





L±T



Note:

L(Length)	T(Tolerance)	Part number	Color
1000	20	SN38-2/07/1BK	BLK
1000	20	SN38-2/07/1WH	WHT
1000	20	SN38-2/07/1GY	GRY
1800	50	SN38-2/07/1.8BK	BLK
1800	50	SN38-2/07/1.8WH	WHT
1800	50	SN38-2/07/1.8GY	GRY
3000	50	SN38-2/07/3BK	BLK
3000	50	SN38-2/07/3WH	WHT
3000	50	SN38-2/07/3GY	GRY
5000	50	SN38-2/07/5BK	BLK
5000	50	SN38-2/07/5WH	WHT
5000	50	SN38-2/07/5GY	GRY



NOTE :

1. PLUG : LT-318 (3A) UNITED KINGDOM TYPE
2. CONNECTOR : LT-503 IEC 60320 C7
3. Strain relief : NA
4. CORD : H03VVH2-F 2X0.75mm²
5. APPROVALS : BSI
6. CUSTOMER : TME
7. Supplier for flexible cord : LIAN DUNG, I-SHENG
8. P/N : Above Note Chart

※Customer drawing number : NA

修改履歷

6		
5		
4		
3		
2		
1	新增	22/09/28
REV.	DESCRIPTION	DATE

DRAWER	Aaron	DATE	22/09/28	TITLE	LT-318+503
APPROVE		REV.	1	Dr.No.	1110969
		比例		TOL.	±5mm
				ALL DIMENSIONS IN mm	



LIAN DUNG
ELECTRIC WIRE MATERIAL CO.,LTD.
聯東電線材料股份有限公司