










REV.	ECN NO.	DATE	SGN	DESCRIPTION
A	Initial Release	2010/09/14	Rex	Change Rev.01 To Rev.A

1	2	3	4	5	6	7	8
---	---	---	---	---	---	---	---



Pin Assignment
Front View

Recommended Panel Cut-Out

- Note:
- * Important Dimension To Check.
 - * Waterproof Rate: IP68 (水深1米, 24hrs)
 - * Connector: Nylon+GF, 94V-0, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Shield: Nylon+GF, 94V-0, Black
 - * Nut: Nylon+GF, 94V-0, Black
 - * O-Ring(Inner): Silicone, Gray, 94V-0
 - * O-Ring(Outer): Silicone, Gray, 94V-0
 - * For Panel Thickness Max 4.0mm

UNIT:mm	TITLE		ITEM NO		DRAWN BY	DATE
TOLERANCE	M12 CONN,PCB		LTW12P-04PFFP-SF8001		Rex	2010/09/17
.X	PANEL SCREW 4PIN F CONN F PIN		DWG NO		CHECKED BY	DATE
.XX	SCALE Free		LTW12P-04PFFP-SF8001		Winnie	2010/09/17
.XXX	REV. A		CUSTOMER		APPROVED BY	DATE
ANGLES	SIZE A4				Kevin	2010/09/17
	SHEET 1 OF 1					
	: Inspection Item					
1	2	3	4	5	6	7

Amphenol LTW
安費諾亮泰企業股份有限公司