


**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |                                                                               |
|------------|-------------------------------------------------------------------------------|
| Type       | A3C 2.5                                                                       |
| Order No.  | <a href="#">1521740000</a>                                                    |
| Version    | Feed-through terminal, PUSH IN, 2.5 mm <sup>2</sup> , 800 V, 24 A, dark beige |
| GTIN (EAN) | 4050118328066                                                                 |
| Qty.       | 100 pc(s).                                                                    |

**A-series  
A3C 2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

|                          |         |                 |            |
|--------------------------|---------|-----------------|------------|
| Width                    | 5.1 mm  | Width (inches)  | 0.201 inch |
| Height                   | 66.5 mm | Height (inches) | 2.618 inch |
| Depth                    | 36.5 mm | Depth (inches)  | 1.437 inch |
| Depth including DIN rail | 37 mm   | Net weight      | 8.031 g    |

**Temperatures**

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max.        | 40 °C         | Storage temperature, min.        | 10 °C  |
| Storage temperature              | 10 °C...40 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C        |                                  |        |

**Material data**

|                                |        |                           |            |
|--------------------------------|--------|---------------------------|------------|
| Material                       | Wemid  | Colour                    | dark beige |
| Colour of operational elements | orange | UL 94 flammability rating | V-0        |

**Rating data IECEx/ATEX**

|                                |                     |                                 |                     |
|--------------------------------|---------------------|---------------------------------|---------------------|
| Certificate No. (ATEX)         | TUEV16ATEX7909U     | Certificate No. (IECEX)         | IECEXTUR16.0036U    |
| Max. voltage (ATEX)            | 550 V               | Current (ATEX)                  | 21 A                |
| Wire cross section max. (ATEX) | 2.5 mm <sup>2</sup> | Max. voltage (IECEX)            | 550 V               |
| Current (IECEX)                | 21 A                | Wire cross section max. (IECEX) | 2.5 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex eb II C Gb       | Ex 2014/34/EU label             | II 2 G D            |

**System specifications**

|                               |       |                                     |    |
|-------------------------------|-------|-------------------------------------|----|
| End cover plate required      | Yes   | Number of potentials                | 1  |
| Number of levels              | 1     | Number of clamping points per level | 3  |
| Number of potentials per tier | 1     | PE connection                       | No |
| Rail                          | TS 35 | N-function                          | No |
| PE function                   | No    | PEN function                        | No |

**Additional technical data**

|                     |       |                   |         |
|---------------------|-------|-------------------|---------|
| Installation advice | Rail  | Open sides        | right   |
| Snap-on             | No    | Type of fixing    | Snap-on |
| Type of mounting    | TS 35 | With snap-in pegs | No      |

**CSA rating data**

|                               |                 |                               |        |
|-------------------------------|-----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-70089609 | Current size B (CSA)          | 20 A   |
| Current size C (CSA)          | 20 A            | Current size D (CSA)          | 5 A    |
| Voltage size B (CSA)          | 600 V           | Voltage size C (CSA)          | 600 V  |
| Voltage size D (CSA)          | 600 V           | Wire cross section max. (CSA) | 12 AWG |
| Wire cross section min. (CSA) | 28 AWG          |                               |        |

**A-series**  
**A3C 2.5**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data**
**Conductors for clamping (rated connection)**

|                                                                                         |                      |                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|----------------------|
| Blade size                                                                              | 0.6 x 3.5 mm         | Clamping range, max.                                                                    | 2.5 mm <sup>2</sup>  |
| Clamping range, min.                                                                    | 0.14 mm <sup>2</sup> | Connection cross-section, stranded, max.                                                | 2.5 mm <sup>2</sup>  |
| Connection cross-section, stranded, min.                                                | 0.5 mm <sup>2</sup>  | Connection direction                                                                    | top                  |
| Gauge to IEC 60947-1                                                                    | A3                   | Number of connections                                                                   | 3                    |
| Stripping length                                                                        | 10 mm                | Twin wire-end ferrules, max.                                                            | 0.75 mm <sup>2</sup> |
| Twin wire-end ferrules, min.                                                            | 0.5 mm <sup>2</sup>  | Type of connection                                                                      | PUSH IN              |
| Wire connection cross section AWG, max.                                                 | AWG 12               | Wire connection cross section AWG, min.                                                 | AWG 28               |
| Wire connection cross section, finely stranded, max.                                    | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>  |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup>  |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>  |
| Wire connection cross-section, solid core, max.                                         | 2.5 mm <sup>2</sup>  | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup>  |

**Rating data**

|                                             |                     |                                              |         |
|---------------------------------------------|---------------------|----------------------------------------------|---------|
| Rated cross-section                         | 2.5 mm <sup>2</sup> | Rated voltage                                | 800 V   |
| Rated current                               | 24 A                | Current at maximum wires                     | 24 A    |
| Standards                                   | IEC 60947-7-1       | Volume resistance according to IEC 60947-7-x | 1.33 mΩ |
| Power loss in accordance with IEC 60947-7-x | 0.77 W              | Rated impulse withstand voltage              | 8 kV    |
| Pollution severity                          | 3                   | Surge voltage category                       | III     |

**UL rating data**

|                                            |        |                                            |        |
|--------------------------------------------|--------|--------------------------------------------|--------|
| Certificate No. (cURus)                    | E60693 | Conductor size Factory wiring max. (cURus) | 12 AWG |
| Conductor size Factory wiring min. (cURus) | 28 AWG | Conductor size Field wiring max. (cURus)   | 12 AWG |
| Conductor size Field wiring min. (cURus)   | 28 AWG | Current size B (cURus)                     | 20 A   |
| Current size C (cURus)                     | 20 A   | Current size D (cURus)                     | 5 A    |
| Voltage size B (cURus)                     | 600 V  | Voltage size C (cURus)                     | 600 V  |
| Voltage size D (cURus)                     | 600 V  |                                            |        |

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0   | EC000897    |
| eClass 9.0  | 27-14-11-20 | eClass 9.1 | 27-14-11-20 |
| eClass 10.0 | 27-14-11-20 |            |             |

## A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Approvals

Approvals



ATEX

ROHS

Conform

### Downloads

|                                             |                                                                                                                                                                                                                                                      |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Attestation of Conformity</a><br><a href="#">ATEX Certificate</a><br><a href="#">IECEX Certificate</a><br><a href="#">CB Test Certificate</a><br><a href="#">DE_PT0101_20160614_037_ISSUE01.pdf</a>                                      |
| Brochure/Catalogue                          | <a href="#">CAT 1 TERM 16/17 EN</a>                                                                                                                                                                                                                  |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                                                                                                                                                                             |
| Engineering Data                            | <a href="#">STEP</a>                                                                                                                                                                                                                                 |
| Tender specification                        | <a href="#">Klippon® Connect 1521740000 DE</a><br><a href="#">Klippon® Connect 1521740000 EN</a>                                                                                                                                                     |
| User Documentation                          | <a href="#">NTI_A3C 2.5.pdf</a><br><a href="#">NTI_ALO 6</a><br><a href="#">StorageConditionsTerminalBlocks</a><br><a href="#">Aderendhülsen für die Klippon® Connect A-Reihe</a><br><a href="#">Wire end ferrules for Klippon® Connect A-series</a> |


### Safety note

|               |                                    |
|---------------|------------------------------------|
| Safety notice | <a href="#">Safety Information</a> |
|---------------|------------------------------------|

### A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**Custom printing**


The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/5 MC SDR             | Version                                                   |
| Order No.  | <a href="#">1609810000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190456597              | Weidmueller, To customer specification                    |
| Qty.       | 200 pc(s).                 |                                                           |
| Type       | DEK 5/5 PLUS MC SDR        | Version                                                   |
| Order No.  | <a href="#">1854500000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4032248393602              | Weidmueller, To customer specification                    |
| Qty.       | 200 pc(s).                 |                                                           |
| Type       | DEK 5/5 S MC SDR           | Version                                                   |
| Order No.  | <a href="#">1341590000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118146042              | Weidmueller, To customer specification                    |
| Qty.       | 80 pc(s).                  |                                                           |

**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**Plus**


The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/5 PLUS MC NE WS      | Version                                                   |
| Order No.  | <a href="#">1854490000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4032248393596              | Weidmueller, white                                        |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 PLUS MC NE GE      | Version                                                   |
| Order No.  | <a href="#">1907520000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4032248532100              | Weidmueller, yellow                                       |
| Qty.       | 1,000 pc(s).               |                                                           |

**Blank**


WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.

WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | WS 10/5 MC NE GE           | Version                                                            |
| Order No.  | <a href="#">1773531687</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141753              | Allen-Bradley, yellow                                              |
| Qty.       | 720 pc(s).                 |                                                                    |


## A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Accessories

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | WS 10/5 PLUS MC NE WS      | Version                                                            |
| Order No.  | <a href="#">1046380000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248782086              | Allen-Bradley, white                                               |
| Qty.       | 600 pc(s).                 |                                                                    |
| Type       | WS 10/5 M MC NE WS         | Version                                                            |
| Order No.  | <a href="#">1792000000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248223862              | Allen-Bradley, white                                               |
| Qty.       | 720 pc(s).                 |                                                                    |
| Type       | WS 10/5 MC NE BL           | Version                                                            |
| Order No.  | <a href="#">1773531693</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141814              | Allen-Bradley, blue                                                |
| Qty.       | 720 pc(s).                 |                                                                    |
| Type       | WS 10/5 MC NE RT           | Version                                                            |
| Order No.  | <a href="#">1773531686</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141746              | Allen-Bradley, red                                                 |
| Qty.       | 720 pc(s).                 |                                                                    |
| Type       | WS 10/5 M PLUS MC NE WS    | Version                                                            |
| Order No.  | <a href="#">2003770000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4050118424447              | Allen-Bradley, white                                               |
| Qty.       | 600 pc(s).                 |                                                                    |
| Type       | WS 10/5 MC NE WS           | Version                                                            |
| Order No.  | <a href="#">1635000000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190261948              | Allen-Bradley, white                                               |
| Qty.       | 720 pc(s).                 |                                                                    |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/5 MC NE BR           | Version                                                   |
| Order No.  | <a href="#">1249870000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118051865              | Weidmueller, brown                                        |
| Qty.       | 1,000 pc(s).               |                                                           |



**A-series**  
**A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**


|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/5 MC NE SW           | Version                                                   |
| Order No.  | <a href="#">1457550000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118263817              | Weidmueller, Black                                        |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 MC NE GR           | Version                                                   |
| Order No.  | <a href="#">1609801691</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397159              | Weidmueller, grey                                         |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 MC NE RT           | Version                                                   |
| Order No.  | <a href="#">1609801686</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397128              | Weidmueller, red                                          |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 MC NE GE           | Version                                                   |
| Order No.  | <a href="#">1609801687</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397135              | Weidmueller, yellow                                       |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 MC NE VI           | Version                                                   |
| Order No.  | <a href="#">1249860000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118042764              | Weidmueller, violet                                       |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 MC NE BL           | Version                                                   |
| Order No.  | <a href="#">1609801693</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397166              | Weidmueller, blue                                         |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 MC NE WS           | Version                                                   |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111              | Weidmueller, white                                        |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 S MC NE WS         | Version                                                   |
| Order No.  | <a href="#">1341620000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118145793              | Weidmueller, white                                        |
| Qty.       | 400 pc(s).                 |                                                           |
| Type       | DEK 5/5 MC NE GN           | Version                                                   |
| Order No.  | <a href="#">1609801688</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397142              | Weidmueller, green                                        |
| Qty.       | 1,000 pc(s).               |                                                           |
| Type       | DEK 5/5 MC NE OR           | Version                                                   |
| Order No.  | <a href="#">1238340000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118062632              | Weidmueller, orange                                       |
| Qty.       | 1,000 pc(s).               |                                                           |

## A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Accessories

### Partition plates



#### Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

#### General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | APP 2                      | Version                    |
| Order No.  | <a href="#">2489090000</a> | A-series, Separation plate |
| GTIN (EAN) | 4050118499308              |                            |
| Qty.       | 50 pc(s).                  |                            |

### End brackets



#### Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

#### General ordering data

|            |                            |                       |
|------------|----------------------------|-----------------------|
| Type       | AEB 35 SCL/1 V0 BK         | Version               |
| Order No.  | <a href="#">2661300000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702187              |                       |
| Qty.       | 20 pc(s).                  |                       |
| Type       | AEB 35 SCL/1 V0 GY         | Version               |
| Order No.  | <a href="#">2661290000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702170              |                       |
| Qty.       | 20 pc(s).                  |                       |
| Type       | AEB 35 SC/1                | Version               |
| Order No.  | <a href="#">1991920000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118376722              |                       |
| Qty.       | 50 pc(s).                  |                       |
| Type       | AEB 35 SC/1 BK             | Version               |
| Order No.  | <a href="#">2475310000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118487114              |                       |
| Qty.       | 50 pc(s).                  |                       |
| Type       | AEB 35 SCL/1 V0            | Version               |
| Order No.  | <a href="#">2661280000</a> | A-series, End bracket |
| GTIN (EAN) | 4050118702163              |                       |
| Qty.       | 20 pc(s).                  |                       |

## A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Accessories

### Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | WS 10/5 MC M SDR           | Version                                                            |
| Order No.  | <a href="#">1792010000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248223879              | Allen-Bradley, To customer specification                           |
| Qty.       | 144 pc(s).                 |                                                                    |
| Type       | WS 10/5 MC SDR             | Version                                                            |
| Order No.  | <a href="#">1635010000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190456634              | Allen-Bradley, To customer specification                           |
| Qty.       | 144 pc(s).                 |                                                                    |
| Type       | WS 10/5 PLUS MC SDR        | Version                                                            |
| Order No.  | <a href="#">1046320000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248782024              | Allen-Bradley, To customer specification                           |
| Qty.       | 120 pc(s).                 |                                                                    |
| Type       | WS 10/5 M PLUS MC SDR      | Version                                                            |
| Order No.  | <a href="#">2007770000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4050118393279              | Allen-Bradley, To customer specification                           |
| Qty.       | 120 pc(s).                 |                                                                    |

**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**V0**


The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                           |
|------------|----------------------------|-----------------------------------------------------------|
| Type       | DEK 5/5 MC NE V0 WS        | Version                                                   |
| Order No.  | <a href="#">1388530000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118188622              | Weidmueller, white                                        |
| Qty.       | 1,000 pc(s).               |                                                           |

**Covers**

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |                            |                                     |
|------------|----------------------------|-------------------------------------|
| Type       | AAM 2.5 YE FLASH           | Version                             |
| Order No.  | <a href="#">2635550000</a> | Terminal marker, 8 x 5.1 mm, yellow |
| GTIN (EAN) | 4050118674095              |                                     |
| Qty.       | 40 pc(s).                  |                                     |

## A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Accessories

### ZQV 2.5N



#### Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

#### General ordering data

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/2 BL              |
| Order No.  | <a href="#">1527740000</a> |
| GTIN (EAN) | 4050118448658              |
| Qty.       | 60 pc(s).                  |
| Type       | ZQV 2.5N/50                |
| Order No.  | <a href="#">1527730000</a> |
| GTIN (EAN) | 4050118411362              |
| Qty.       | 5 pc(s).                   |
| Type       | ZQV 2.5N/2                 |
| Order No.  | <a href="#">1527540000</a> |
| GTIN (EAN) | 4050118448467              |
| Qty.       | 60 pc(s).                  |
| Type       | ZQV 2.5N/3                 |
| Order No.  | <a href="#">1527570000</a> |
| GTIN (EAN) | 4050118448450              |
| Qty.       | 60 pc(s).                  |
| Type       | ZQV 2.5N/7 BL              |
| Order No.  | <a href="#">1527830000</a> |
| GTIN (EAN) | 4050118448603              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/20 BL             |
| Order No.  | <a href="#">1527890000</a> |
| GTIN (EAN) | 4050118448566              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/5 BL              |
| Order No.  | <a href="#">1527790000</a> |
| GTIN (EAN) | 4050118448627              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/5 RD              |
| Order No.  | <a href="#">2108710000</a> |
| GTIN (EAN) | 4050118448511              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/8 BL              |
| Order No.  | <a href="#">1527840000</a> |
| GTIN (EAN) | 4050118448597              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/2 RD              |
| Order No.  | <a href="#">2108470000</a> |
| GTIN (EAN) | 4050118448542              |
| Qty.       | 60 pc(s).                  |

**A-series**  
**A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/7                 |
| Order No.  | <a href="#">1527640000</a> |
| GTIN (EAN) | 4050118448412              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/9                 |
| Order No.  | <a href="#">1527680000</a> |
| GTIN (EAN) | 4050118447996              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/10                |
| Order No.  | <a href="#">1527690000</a> |
| GTIN (EAN) | 4050118447989              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/50 BL             |
| Order No.  | <a href="#">1527920000</a> |
| GTIN (EAN) | 4050118448559              |
| Qty.       | 5 pc(s).                   |
| Type       | ZQV 2.5N/4 RD              |
| Order No.  | <a href="#">2108700000</a> |
| GTIN (EAN) | 4050118448528              |
| Qty.       | 60 pc(s).                  |
| Type       | ZQV 2.5N/6                 |
| Order No.  | <a href="#">1527630000</a> |
| GTIN (EAN) | 4050118448429              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/9 RD              |
| Order No.  | <a href="#">2108900000</a> |
| GTIN (EAN) | 4050118448474              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/50 RD             |
| Order No.  | <a href="#">2109000000</a> |
| GTIN (EAN) | 4050118486001              |
| Qty.       | 5 pc(s).                   |
| Type       | ZQV 2.5N/20                |
| Order No.  | <a href="#">1527720000</a> |
| GTIN (EAN) | 4050118447972              |
| Qty.       | 20 pc(s).                  |
| Type       | ZQV 2.5N/4 BL              |
| Order No.  | <a href="#">1527780000</a> |
| GTIN (EAN) | 4050118448634              |
| Qty.       | 60 pc(s).                  |
| Type       | ZQV 2.5N/3 BL              |
| Order No.  | <a href="#">1527770000</a> |
| GTIN (EAN) | 4050118448641              |
| Qty.       | 60 pc(s).                  |
| Type       | ZQV 2.5N/4                 |
| Order No.  | <a href="#">1527590000</a> |
| GTIN (EAN) | 4050118448443              |
| Qty.       | 60 pc(s).                  |
| Type       | ZQV 2.5N/10 RD             |
| Order No.  | <a href="#">2108910000</a> |
| GTIN (EAN) | 4050118486018              |
| Qty.       | 20 pc(s).                  |

## A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/20 RD             |
| Order No.  | <a href="#">2108920000</a> |
| GTIN (EAN) | 4050118485899              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/10 BL             |
| Order No.  | <a href="#">1527880000</a> |
| GTIN (EAN) | 4050118448573              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/7 RD              |
| Order No.  | <a href="#">2108810000</a> |
| GTIN (EAN) | 4050118448498              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/6 BL              |
| Order No.  | <a href="#">1527820000</a> |
| GTIN (EAN) | 4050118448610              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/5                 |
| Order No.  | <a href="#">1527620000</a> |
| GTIN (EAN) | 4050118448436              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/9 BL              |
| Order No.  | <a href="#">1527870000</a> |
| GTIN (EAN) | 4050118448580              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/3 RD              |
| Order No.  | <a href="#">2108690000</a> |
| GTIN (EAN) | 4050118448535              |
| Qty.       | 60 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/6 RD              |
| Order No.  | <a href="#">2108720000</a> |
| GTIN (EAN) | 4050118448504              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/8                 |
| Order No.  | <a href="#">1527670000</a> |
| GTIN (EAN) | 4050118448405              |
| Qty.       | 20 pc(s).                  |

|            |                            |
|------------|----------------------------|
| Type       | ZQV 2.5N/8 RD              |
| Order No.  | <a href="#">2108870000</a> |
| GTIN (EAN) | 4050118448481              |
| Qty.       | 20 pc(s).                  |

**A-series**  
**A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**Blank**


WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | WS 8/5 MC NE BL            | Version                                                           |
| Order No.  | <a href="#">1773521693</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141715              | Allen-Bradley, blue                                               |
| Qty.       | 720 pc(s).                 |                                                                   |
| Type       | WS 8/5 MC NE RT            | Version                                                           |
| Order No.  | <a href="#">1773521686</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141531              | Allen-Bradley, red                                                |
| Qty.       | 720 pc(s).                 |                                                                   |
| Type       | WS 8/5 MC NE GE            | Version                                                           |
| Order No.  | <a href="#">1773521687</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141548              | Allen-Bradley, yellow                                             |
| Qty.       | 720 pc(s).                 |                                                                   |
| Type       | WS 8/5 MC NE OR            | Version                                                           |
| Order No.  | <a href="#">1773521690</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248143092              | Allen-Bradley, orange                                             |
| Qty.       | 720 pc(s).                 |                                                                   |
| Type       | WS 8/5 MC NE WS            | Version                                                           |
| Order No.  | <a href="#">1640740000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190279103              | Allen-Bradley, white                                              |
| Qty.       | 720 pc(s).                 |                                                                   |
| Type       | WS 8/5 PLUS MC NE WS       | Version                                                           |
| Order No.  | <a href="#">1951870000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248631605              | Allen-Bradley, white                                              |
| Qty.       | 600 pc(s).                 |                                                                   |



**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****End plates****Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |                            |                     |
|------------|----------------------------|---------------------|
| Type       | AEP 3C 2.5 BL              | Version             |
| Order No.  | <a href="#">1521520000</a> | A-series, End plate |
| GTIN (EAN) | 4050118328356              |                     |
| Qty.       | 50 pc(s).                  |                     |
| Type       | AEP 3C 2.5 OR              | Version             |
| Order No.  | <a href="#">2052300000</a> | A-series, End plate |
| GTIN (EAN) | 4050118411966              |                     |
| Qty.       | 50 pc(s).                  |                     |
| Type       | AEP 3C 2.5                 | Version             |
| Order No.  | <a href="#">1521510000</a> | A-series, End plate |
| GTIN (EAN) | 4050118328417              |                     |
| Qty.       | 50 pc(s).                  |                     |

**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories****WS 8/5****WS/ DEK**

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

|            |                            |                                                   |
|------------|----------------------------|---------------------------------------------------|
| Type       | WS 8/5 MM WS               | Version                                           |
| Order No.  | <a href="#">2007150000</a> | WS, Terminal marker, 8 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392029              |                                                   |
| Qty.       | 800 pc(s).                 |                                                   |

**Digital multimeters**

Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

**General ordering data**

|            |                            |            |
|------------|----------------------------|------------|
| Type       | ZUB MULTIMETER             | Version    |
| Order No.  | <a href="#">9205270000</a> | Multimeter |
| GTIN (EAN) | 4032248723522              |            |
| Qty.       | 1 pc(s).                   |            |

**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**Test adapter**

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | ATPG 2.5/5                 |
| Order No.  | <a href="#">2041180000</a> |
| GTIN (EAN) | 4050118409505              |
| Qty.       | 25 pc(s).                  |
| Type       | ATPG 2.5/3                 |
| Order No.  | <a href="#">2041190000</a> |
| GTIN (EAN) | 4050118409604              |
| Qty.       | 25 pc(s).                  |
| Type       | ATPG 2.5 MI-R              |
| Order No.  | <a href="#">1991960000</a> |
| GTIN (EAN) | 4050118376685              |
| Qty.       | 50 pc(s).                  |
| Type       | ATPG 1.5-10 L              |
| Order No.  | <a href="#">1991890000</a> |
| GTIN (EAN) | 4050118376647              |
| Qty.       | 50 pc(s).                  |

**Slotted screwdriver**


VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

**General ordering data**

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | SDIL 0,6x3,5x100           | Version                                                            |
| Order No.  | <a href="#">9042110000</a> | Screwdriver, Blade width (B): 3.5 mm, 100 mm, Blade thickness (A): |
| GTIN (EAN) | 4008190347796              | 0.6 mm, Yes                                                        |
| Qty.       | 1 pc(s).                   |                                                                    |

**A-series  
A3C 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**
**DEK 5/5**

**WS/ DEK**

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

**Your benefits with MultiMark**

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

**General ordering data**

|            |                            |                                                        |
|------------|----------------------------|--------------------------------------------------------|
| Type       | DEK 5/5 MM WS              | Version                                                |
| Order No.  | <a href="#">2007110000</a> | Dekafix, Terminal marker, 5 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118391862              |                                                        |
| Qty.       | 800 pc(s).                 |                                                        |

**Custom printing**


WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | WS 8/5 MC SDR              | Version                                                           |
| Order No.  | <a href="#">1640750000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190456627              | Allen-Bradley, To customer specification                          |
| Qty.       | 144 pc(s).                 |                                                                   |

### A-series A3C 2.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

| Type       | WS 8/5 PLUS MC SDR         | Version                                                           |  |
|------------|----------------------------|-------------------------------------------------------------------|--|
| Order No.  | <a href="#">1038790000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |  |
| GTIN (EAN) | 4032248768066              | Allen-Bradley, To customer specification                          |  |
| Qty.       | 120 pc(s).                 |                                                                   |  |