

Electronic housing - EH 90 F-B/ABS BK9005 - 2200664

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component housing, color: black, width: 90 mm

Why buy this product

- ✓ Item is part of the EH product range
- ✓ Tool-free mounting
- ✓ Available in overall widths from 22.5 mm ... 90 mm
- ✓ Inflammability class HB acc. to UL 94
- ✓ Variety of connection technologies
- ✓ Can be mounted on the DIN rail or the wall

RoHS

Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 046356 911139
GTIN	4046356911139
Weight per Piece (excluding packing)	34.930 g
Custom tariff number	85472000
Country of origin	India

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Dimensions

Width	90 mm
-------	-------

Technical data

Power dissipation without gap	9.8 W
Power dissipation with 20 mm gap	16.4 W

Electronic housing - EH 90 F-B/ABS BK9005 - 2200664

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031

UNSPSC

UNSPSC 13.2	31261501
-------------	----------

Accessories

Accessories

Mounting material

Electronic housing - EH SNAPLOCK SET WALL MOUNT OG - 2202007

Component housing, color: orange



Necessary add-on products

Housing cover - EH 90 F-C CS/ABS BK9005 - 2201776



Component housing, without connection opening, Upper part, color: black, width: 90 mm

Electronic housing - EH 90 F-B/ABS BK9005 - 2200664

Accessories

Housing cover - EH 90 F-C CS/ABS GY7035 - 2201777



Component housing, without connection opening, Upper part, color: gray, width: 90 mm

Housing cover - EH 90 F-C DS/ABS BK9005 - 2201779



Component housing, connection opening on both sides, Upper part, color: black, width: 90 mm

Housing cover - EH 90 F-C DS/ABS GY7035 - 2201778



Component housing, connection opening on both sides, Upper part, color: gray, width: 90 mm

Housing cover - EH 90 F-C SS/ABS BK9005 - 2201388



Component housing, connection opening on one side, Upper part, color: black, width: 90 mm

Housing cover - EH 90 F-C SS/ABS GY7035 - 2201282



Component housing, connection opening on one side, Upper part, color: gray, width: 90 mm
