S/FTP Cat. 6A LSZH patch cord, black, 1.5 m

PP6A-LSZHCU-BK-1.5M

- Perfect connection
- Dual shielded for a reliable connection
- Low Smoke Zero Halogen (LSZH) jacket
- Gold plated contacts

Features

- Patch cord with foil shielded pairs and braided cable, CAT 6A
- Gold plated contacts
- Low Smoke Zero Halogen (LSZH) jacket
- Molded strain reliefs
- Snagless boots

Specifications

Patch cord category 6A SSTP (shielded)
Length: according to the item
Structure: AWG 27 (7 x 0.135 mm wire), COPPER
FM-PE insulation of the wire: 1.0 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: not used
With Braid : 16 x 4/0.12mm
Outer insulation: 5.8 mm
Color: according to the item
Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs	150
Crtn volume, CUM	0.041
Crtn weight, kgs	8.48
Individual package size LxWxH:	130x10x170 mm
Carton size LxWxH:	400x300x340 mm
Country of origin	CN
Barcode	8716309091282
Customs code	8544421000

Certificates

Copyright © 2009–2022, Gembird Software Ltd.

Wittevrouwen 56 | 1358CD Almere | The Netherlands | Phone: +31-36-5211588
www.cablexpert.com | postmaster@cablexpert.com