REV.	DATE	DESCRIPTION
NC	01/07/04	UPDATE DRAWING FORMAT
A	08/04/05	ADD "75ohm" TO PART DESCRIPTION



	DESCRIPTION	MATERIAL	FINISH	QTY
8				
7				
6				
5				
4				
3	CONTACT PIN	BRASS	GOLD	1
2	INSULATOR	DELRIN	NATURAL	1
1	BODY	BRASS	NICKEL	1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERANCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 – 8mm ± 0.20mm
8 – 30mm ± 0.40mm
30 – 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 – .315 = ± 0.007"
.315 – 1.180 = ± 0.015"
1.180 – 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS		DATE
DRAWN	G.R.S.	08/04/05
CHECKED		
ISSUED		
SHEET	1 OF 1	
CAD FILE	C:/112/112448.DWG	

Amphenol Connex

PART DESCRIPTION
BNC MALE TO BNC MALE ADAPTER (75ohm)

PART NO. 112448

DWG. NO.	REV.	SIZE	SCALE
112448.DWG	A	A	NA