




NEO

SPECIALLY DESIGNED FOR

- Industrial Control
- IoT
- Building Automation



HINGED POLYCARBONATE ENCLOSURE

WITH GREY COVER

Specification:

- IP 66 / 67
- IK 09

Features and benefits:

- High mechanical impact resistant
- Outdoor and UV resistant
- Ambient temperature
- Flame retardant
- Chemical resistant
- Modern outlook
- Radio frequency transparent



Dimensions	Code	Symbol
320 x 220 x 150 mm	4810000	NEO PC 322215 G
320 x 320 x 150 mm	4810001	NEO PC 323215 G
420 x 320 x 150 mm	4810002	NEO PC 423215 G

HINGED POLYCARBONATE ENCLOSURE

WITH TRANSPARENT COVER

Specification:

- IP 66 / 67
- IK 09

Features:

- Large viewing window
- High mechanical impact resistant
- Outdoor and UV resistant
- Ambient temperature
- Flame retardant
- Chemical resistant
- Modern outlook
- Radio frequency transparent



Dimensions	Code	Symbol
320 x 220 x 150 mm	4811000	NEO PC 322215 T
320 x 320 x 150 mm	4811001	NEO PC 323215 T
420 x 320 x 150 mm	4811002	NEO PC 423215 T

HINGED ABS ENCLOSURE

WITH GREY COVER

Specification:

- IP 66 / 67
- IK 08

Features:

- Light weight
- Designed for indoor applications
- Easy installation and servicing
- Radio frequency transparent



Dimensions	Code	Symbol
320 x 220 x 150 mm	4812000	NEO ABS 322215 G
320 x 320 x 150 mm	4812001	NEO ABS 323215 G
420 x 320 x 150 mm	4812002	NEO ABS 423215 G

ACCESSORIES

Wall Mounting Lug Sets:

- Quick installation
- Access for cables behind enclosure



Mounting Plates Metal:

- Extra installation space
- Easy machining



Multi perforated Mounting Plates Plastic:

- Radio frequency transparent
- Quick installation
- Light weight



Pole Mounting Kit:

- Easy and secure installation



Accessories	Dimensions	Code	Symbol
Wall Mounting Lug Sets		4850001	WMK NEO plastic
Mounting Plates Metal	275 x 165 x 1,5 mm	4850060	NEO MPS 3222
	275 x 265 x 1,5 mm	4850061	NEO MPS 3232
	375 x 265 x 1,5 mm	4850062	NEO MPS 4232
Mounting Plates Plastic	275 x 165 x 3 mm	4850070	NEO MPI 3222
	275 x 265 x 3 mm	4850071	NEO MPI 3232
	375 x 265 x 3 mm	4850072	NEO MPI 4232
Pole Mounting Kit		4850050	PMK NEO 20
		4850051	PMK NEO 30

Protective and robust

- High ingress protection
- Non corroding
- Maintenance free
- Double insulated
- Double walled base corners
- Reinforced cover design
- Wide protective gasket
- Robust stainless steel cover screws
- Integrated rain canopy
- Industrial design



Efficient

- Hinged with two cover screws for easy servicing
- Extensive surface areas for customizing
- Extra installation space
- Quick installation
- Easy machining
- Installation outside the protected gasket area
- Door opening angle more than 180°
- Easy access to the contents

