

Product information

00 21 34 HL S2

Tool Case “Robust23 Start” Electric 24 parts



Robust tool case with basic equipment for mobile electrical professionals

- Equipped with 6 KNIPEX tools, a total of 24 brand tools
- For the toughest conditions: Dust-tight, waterproof and temperature-resistant
- Max. payload: 25 kg
- Volume: 23 litres
- Fit-to-fly case, made from impact-resistant polypropylene
- Tool panels made of dirt-repellent PP twin-wall sheets with tool pockets and straps
- Base tray with aluminium inserts
- Air pressure compensation valve
- Temperature-resistant from - 30°C to +80° C
- Padlock eyelets
- Dimensions exterior (W x H x D): 470 x 370 x 190 mm; dimensions interior (W x H x D): 437 x 307 x 172 mm

General

Article No.	00 21 34 HL S2
EAN	4003773087366
Weight	6,800 g
Reach	no
RohS	no

Technical details

Dimension exterior (interior) width mm	470 mm (437 mm)
Dimension exterior (interior) height mm	370 mm (307 mm)
Dimension exterior (interior) depth mm	190 mm (172 mm)

Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076

Content

11 06 160	1 x Insulation Stripper with opening spring, universal (Ø 5,0 mm / 10,0 mm²) ⚡ 1000V 
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool (Ø 8,0 – 13,0 mm) 
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚡ 1000V 
70 06 160	1 x Diagonal Cutter ⚡ 1000V 

Content	
97 78 180	1 x Crimping Pliers for wire ferrules (0,25 – 16 mm ²) ⚡ 1000V 
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)
031580	1 x Wera Screwdrivers for slotted screws 1160i (0,4 x 2,5 x 80 mm)
031582	1 x Wera Screwdrivers for slotted screws 1160i (0,6 x 3,5 x 100 mm)
031587	1 x Wera Screwdrivers for slotted screws 1160i (1,0 x 5,5 x 125 mm)
031588	1 x Wera Screwdrivers for slotted screws 1160i (1,2 x 6,5 x 150 mm)
031601	1 x Wera Screwdrivers for cross recessed Phillips® screws 1162i (PH1 x 80 mm)
031603	1 x Wera Screwdrivers for cross recessed Phillips® screws 1162i (PH2 x 100 mm)
31611	1 x Wera Screwdrivers for cross recessed Pozidriv® screws 1165i (PZ1 x 80 mm)
31613	1 x Wera Screwdrivers for cross recessed Pozidriv® screws 1165i (PZ2 x 100 mm)

technical change and errors excepted

