



EAN:	4013288196576	Size:	122x83x22 mm
Part number:	05078691001	Weight:	137 g
Article number:	7781	Country of origin:	TW
		Customs tariff number:	82079099

- Square insert tool 14x18 mm
- For torque wrenches of the Click-Torque X series with 14x18 mm holder
- Application: Hexagon screw heads or nuts
- With safety pin
- The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads

Ring spanner insert, for hexagon screw heads or nuts; for torque wrenches of the Click-Torque X series with 14x18 mm holder.

Web link

https://products.wera.de/en/torque_tools_series_click-torque_wrenches_series_insert_tools_7781.html

Wera - 7781

05078691001 - 4013288196576

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Series Insert Tools

Drive 14x18 mm

Chrome vanadium steel

With safety pin



For torque wrenches of the Click-Torque X series with 14x18 mm holder.



The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads.



The safety pin of the insert tools enables safe working and fast tool change.

Further versions in this product family:

					
	mm	mm	mm	mm	mm
05078690001	13	62.0	37.0	30	11.0
05078691001	14	62.0	37.0	30.0	11.0
05078692001	15	62.0	37.0	30.0	11.0
05078693001	16	64.0	39.0	28.0	12.0
05078694001	17	64.0	39.0	28.0	12.0
05078695001	18	64.0	39.0	28.0	12.0
05078696001	19	64.0	39.0	28.0	12.0
05078697001	21	64.0	39.0	28.0	12.0
05078698001	22	64.0	39.0	28.0	12.0
05078699001	24	64.0	39.0	28.0	12.0
05078700001	27	81.0	56.0	53.0	21.0
05078701001	30	81.0	56.0	53.0	21.0
05078702001	32	81.0	56.0	53.0	21.0
05078703001	34	81.0	56.0	53.0	21.0
05078704001	36	81.0	56.0	53.0	21.0
05078705001	41	81.0	56.0	53.0	21.0

Web link

https://products.wera.de/en/torque_tools_series_click-torque_wrenches_series_insert_tools_7781.html

Wera - 7781

05078691001 - 4013288196576

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de