



|                        |                  |                               |           |
|------------------------|------------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288094254    | <b>Size:</b>                  | 89x7x6 mm |
| <b>Part number:</b>    | 05059630001      | <b>Weight:</b>                | 11 g      |
| <b>Article number:</b> | 840/4 Z Hex-Plus | <b>Country of origin:</b>     | CZ        |
|                        |                  | <b>Customs tariff number:</b> | 82079030  |

- For socket head screws
- Ductile and tough for hard materials
- Hex-Plus allows socket head screws to live longer
- 1/4" hexagon drive (Wera connecting series 4)
- Suitable for AEG, ARO, Atlas-Copco, Biax, Black & Decker, Bosch, Buckeye Tools etc.

Tough viscous Wera bits for hexagon socket screws for universal use. The Hex-Plus profile offers a greater contact surface in the head of the screw. The notching effect is therefore reduced to a minimum and damage to the screw head more or less eliminated. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

**Web link**

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_hexagon\\_socket\\_screws\\_840\\_4\\_z\\_hex-plus.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html)

Wera - 840/4 Z Hex-Plus  
05059630001 - 4013288094254

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Bits for Hexagon Socket Screws

## Hex-Plus



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

## Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

## Further versions in this product family:

|                    |  |  |  |  |  |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    | mm                                                                                  | inch                                                                                | mm                                                                                  | inch                                                                                  | mm                                                                                    |
| 05160885001        | 0.9                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 2.6                                                                                   |
| 05059602001        | 1.5                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 2.0                                                                                   |
| 05059603001        | 2.0                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 4.0                                                                                   |
| 05059628001        | 2.0                                                                                 |                                                                                     | 89                                                                                  | 3 1/2                                                                                 | 4.0                                                                                   |
| 05059604001        | 2.5                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 4.0                                                                                   |
| 05059629001        | 2.5                                                                                 |                                                                                     | 89                                                                                  | 3 1/2                                                                                 | 4.0                                                                                   |
| 05059605001        | 3.0                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 4.0                                                                                   |
| <b>05059630001</b> | <b>3.0</b>                                                                          |                                                                                     | <b>89</b>                                                                           | <b>3 1/2</b>                                                                          | <b>4.0</b>                                                                            |
| 05380033001        | 3.0                                                                                 |                                                                                     | 152                                                                                 | 6                                                                                     | 4.0                                                                                   |
| 05059610001        | 4.0                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 5.0                                                                                   |
| 05059631001        | 4.0                                                                                 |                                                                                     | 89                                                                                  | 3 1/2                                                                                 | 5.0                                                                                   |
| 05059634001        | 4.0                                                                                 |                                                                                     | 152                                                                                 | 6                                                                                     | 5.0                                                                                   |
| 05059615001        | 5.0                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 6.0                                                                                   |
| 05059632001        | 5.0                                                                                 |                                                                                     | 89                                                                                  | 3 1/2                                                                                 | 6.0                                                                                   |
| 05059635001        | 5.0                                                                                 |                                                                                     | 152                                                                                 | 6                                                                                     | 6.0                                                                                   |
| 05059620001        | 6.0                                                                                 |                                                                                     | 50                                                                                  | 2                                                                                     | 5.0                                                                                   |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_hexagon\\_socket\\_screws\\_840\\_4\\_z\\_hex-plus.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html)

Wera - 840/4 Z Hex-Plus  
 05059630001 - 4013288094254

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: [info@wera.de](mailto:info@wera.de)

## Bits for Hexagon Socket Screws

|             |       |     |       |     |
|-------------|-------|-----|-------|-----|
| 05059633001 | 6.0   | 89  | 3 1/2 | -   |
| 05059636001 | 6.0   | 152 | 6     | -   |
| 05059625001 | 8.0   | 50  | 2     | -   |
| 05059637001 | 8.0   | 89  | 3 1/2 | -   |
| 05350430001 | 0.05  | 50  | 2     | 2.5 |
| 05135090001 | 1/16" | 50  | 2     | 2.5 |
| 05135091001 | 5/64" | 50  | 2     | 3.0 |
| 05059660001 | 5/64" | 89  | 3 1/2 | 3.0 |
| 05135092001 | 3/32" | 50  | 2     | 3.0 |
| 05059661001 | 3/32" | 89  | 3 1/2 | 3.5 |
| 05135093001 | 7/64" | 50  | 2     | 3.5 |
| 05059662001 | 7/64" | 89  | 3 1/2 | 4.0 |
| 05135094001 | 1/8"  | 50  | 2     | 4.0 |
| 05059663001 | 1/8"  | 89  | 3 1/2 | 4.0 |
| 05380045001 | 1/8"  | 152 | 6     | 4.0 |
| 05135095001 | 9/64" | 50  | 2     | 4.5 |
| 05059664001 | 9/64" | 89  | 3 1/2 | 4.5 |
| 05380046001 | 9/64" | 152 | 6     | 4.5 |
| 05135096001 | 5/32" | 50  | 2     | 5.0 |
| 05059665001 | 5/32" | 89  | 3 1/2 | 5.0 |
| 05380047001 | 5/32" | 152 | 6     | 5.0 |
| 05135097001 | 3/16" | 50  | 2     | 6.0 |
| 05059666001 | 3/16" | 89  | 3 1/2 | 6.0 |
| 05380048001 | 3/16" | 152 | 6     | 6.0 |
| 05135098001 | 7/32" | 50  | 2     | -   |
| 05059667001 | 7/32" | 89  | 3 1/2 | -   |
| 05380049001 | 7/32" | 152 | 6     | -   |
| 05135099001 | 1/4"  | 50  | 2     | -   |
| 05059668001 | 1/4"  | 89  | 3 1/2 | -   |
| 05380050001 | 1/4"  | 152 | 6     | -   |
| 05346288001 | 5/16  | 50  | 2     | -   |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_hexagon\\_socket\\_screws\\_840\\_4\\_z\\_hex-plus.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_hexagon_socket_screws_840_4_z_hex-plus.html)

Wera - 840/4 Z Hex-Plus  
05059630001 - 4013288094254

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)