

Bits for Phillips Screws



EAN:	4013288190444	Size:	44x4x4 mm
Part number:	05134605001	Weight:	3 g
Article number:	851/9 C	Country of origin:	CZ
		Customs tariff number:	82079030

- For Phillips screws
- Hard design
- Optimised for Japanese Phillips screws
- 4 mm halfmoon drive (Wera connecting series 9)
- Suitable for Delvo, Densei, etc.

High quality bits with 4 mm halfmoon drive. Optimised for Japanese PH screws. Hard design.

Web link


https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_phillips_screws_851_9_c.html

Wera - 851/9 C
05134605001 - 4013288190444

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for Phillips Screws

4 mm Halfmoon direct drive



Halfmoon, 4mm, Wera Series 9.
 Drive: For direct machine drive.
 Suitable for: Delvo, Densei etc.

Further versions in this product family:

						
		mm	inch	mm	mm	inch
05134605001¹⁾	PH 000	44	1 47/64	1.5	20	25/32
05134606001 ¹⁾	PH 000	64	2 33/64	1.5	20	25/32
05135270001 ¹⁾	PH 00	44	1 47/64	1.8	20	25/32
05135271001 ¹⁾	PH 00	64	2 33/64	1.8	20	25/32
05135272001 ²⁾	PH 0	44	1 47/64	1.8	20	25/32
05135273001 ²⁾	PH 0	64	2 33/64	1.8	20	25/32
05135274001 ²⁾	PH 0	44	1 47/64	2.0	20	25/32
05135275001 ²⁾	PH 0	64	2 33/64	2.2	20	25/32
05135278001 ²⁾	PH 0	44	1 47/64	2.2	20	25/32
05135276001 ¹⁾	PH 1	44	1 47/64	3.0	20	25/32
05135277001 ¹⁾	PH 1	64	2 33/64	3.0	20	25/32
05134607001	PH 2	44	1 47/64	4.0	-	-
05134608001	PH 2	64	2 33/64	4.0	-	-

1) Optimised for Asian PH screws

2) Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_phillips_screws_851_9_c.html

Wera - 851/9 C

05134605001 - 4013288190444

Wera Werkzeuge GmbH
 Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de