



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288034724 | <b>Size:</b>                  | 25x7x7 mm |
| <b>Part number:</b>    | 05134701001   | <b>Weight:</b>                | 5 g       |
| <b>Article number:</b> | 867/1 IPR     | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For recessed TORX PLUS® IPR screws with safety pin
- Ductile and tough for hard materials
- TORX PLUS® IPR bit with bore hole on the output side
- 1/4" hexagon drive (Wera connecting series 1)
- Suitable for Bosch, Fein, Holz-Her, Leclercx, Metabo

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. Tough viscous for universal use. 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

**Web link**

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_tamper-proof\\_torx\\_plus\\_ipr\\_screws\\_with\\_safety\\_pin\\_867\\_1\\_ipr.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_1_ipr.html)

Wera - 867/1 IPR  
05134701001 - 4013288034724

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Bits for Tamper-proof TORX PLUS® IPR Screws with Safety Pin

For recessed TORX PLUS® IPR screws with safety pin

Tough-absorbing bits



A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

## Further versions in this product family:

|                    |  | <br>mm | <br>inch |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|
| 05134699001        | 8 IPR                                                                              | 25                                                                                       | 1                                                                                            |
| 05134698001        | 9 IPR                                                                              | 25                                                                                       | 1                                                                                            |
| 05134700001        | 10 IPR                                                                             | 25                                                                                       | 1                                                                                            |
| <b>05134701001</b> | <b>15 IPR</b>                                                                      | <b>25</b>                                                                                | <b>1</b>                                                                                     |
| 05134702001        | 20 IPR                                                                             | 25                                                                                       | 1                                                                                            |
| 05134703001        | 25 IPR                                                                             | 25                                                                                       | 1                                                                                            |
| 05134704001        | 27 IPR                                                                             | 25                                                                                       | 1                                                                                            |
| 05134705001        | 30 IPR                                                                             | 25                                                                                       | 1                                                                                            |
| 05134706001        | 40 IPR                                                                             | 35                                                                                       | 1 3/8                                                                                        |
| 05134707001        | 45 IPR                                                                             | 35                                                                                       | 1 3/8                                                                                        |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_tamper-proof\\_torx\\_plus\\_ipr\\_screws\\_with\\_safety\\_pin\\_867\\_1\\_ipr.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_1_ipr.html)

Wera - 867/1 IPR  
05134701001 - 4013288034724

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)