



EAN:	4013288034823	Size:	25x7x7 mm
Part number:	05134700001	Weight:	5 g
Article number:	867/1 IPR	Country of origin:	CZ
		Customs tariff number:	82079030

- For recessed TORX PLUS® IPR screws with safety pin
- Ductile and tough for hard materials
- TORX PLUS® IPR bit with bore hole on the output side
- 1/4" hexagon drive (Wera connecting series 1)
- Suitable for Bosch, Fein, Holz-Her, Leclercx, Metabo

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. Tough viscous for universal use. 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_1_ipr.html

Wera - 867/1 IPR
05134700001 - 4013288034823

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for Tamper-proof TORX PLUS® IPR Screws with Safety Pin

For recessed TORX PLUS® IPR screws with safety pin

Tough-absorbing bits



A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Further versions in this product family:

				
			mm	inch
05134699001	8 IPR		25	1
05134698001	9 IPR		25	1
05134700001	10 IPR		25	1
05134701001	15 IPR		25	1
05134702001	20 IPR		25	1
05134703001	25 IPR		25	1
05134704001	27 IPR		25	1
05134705001	30 IPR		25	1
05134706001	40 IPR		35	1 3/8
05134707001	45 IPR		35	1 3/8

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_1_ipr.html

Wera - 867/1 IPR
 05134700001 - 4013288034823

Wera Werkzeuge GmbH
 Korzenter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de