


VOLTAGE INVERTER IPS-400

12 VDC - 230VAC 400W

	<table> <tr><td>Input voltage:</td><td>11V ÷ 15V</td></tr> <tr><td>Voltage shutdown:</td><td>10V</td></tr> <tr><td>Output voltage:</td><td>230VAC</td></tr> <tr><td>Surge power:</td><td>400VA</td></tr> <tr><td>Rated power:</td><td>200VA</td></tr> <tr><td>Output wave form:</td><td>Modified sine wave</td></tr> <tr><td>Motor soft start:</td><td>NO</td></tr> <tr><td>Overload protection:</td><td>YES</td></tr> <tr><td>Shortcut protection:</td><td>YES</td></tr> <tr><td>Thermal protection:</td><td>YES</td></tr> <tr><td>Overvoltage protection:</td><td>15 VDC</td></tr> <tr><td>Low voltage alarm:</td><td>YES</td></tr> <tr><td>Operating temperature:</td><td>0 ~ +40°C</td></tr> <tr><td>Efficiency:</td><td>> 85%</td></tr> <tr><td>Cooling:</td><td>Active</td></tr> <tr><td>Terminals:</td><td>Car Cigarette Plug</td></tr> <tr><td>230V socket:</td><td>1 pcs</td></tr> <tr><td>Case:</td><td>Aluminium</td></tr> <tr><td>Protection:</td><td>IP21</td></tr> <tr><td>Dimensions [mm]:</td><td>145x76x54</td></tr> <tr><td>Weight [kg]:</td><td>0.365 kg</td></tr> <tr><td>Product code:</td><td>5905279203655</td></tr> </table>	Input voltage:	11V ÷ 15V	Voltage shutdown:	10V	Output voltage:	230VAC	Surge power:	400VA	Rated power:	200VA	Output wave form:	Modified sine wave	Motor soft start:	NO	Overload protection:	YES	Shortcut protection:	YES	Thermal protection:	YES	Overvoltage protection:	15 VDC	Low voltage alarm:	YES	Operating temperature:	0 ~ +40°C	Efficiency:	> 85%	Cooling:	Active	Terminals:	Car Cigarette Plug	230V socket:	1 pcs	Case:	Aluminium	Protection:	IP21	Dimensions [mm]:	145x76x54	Weight [kg]:	0.365 kg	Product code:	5905279203655
Input voltage:	11V ÷ 15V																																												
Voltage shutdown:	10V																																												
Output voltage:	230VAC																																												
Surge power:	400VA																																												
Rated power:	200VA																																												
Output wave form:	Modified sine wave																																												
Motor soft start:	NO																																												
Overload protection:	YES																																												
Shortcut protection:	YES																																												
Thermal protection:	YES																																												
Overvoltage protection:	15 VDC																																												
Low voltage alarm:	YES																																												
Operating temperature:	0 ~ +40°C																																												
Efficiency:	> 85%																																												
Cooling:	Active																																												
Terminals:	Car Cigarette Plug																																												
230V socket:	1 pcs																																												
Case:	Aluminium																																												
Protection:	IP21																																												
Dimensions [mm]:	145x76x54																																												
Weight [kg]:	0.365 kg																																												
Product code:	5905279203655																																												

Inverter description



www.powerinverters.pl



PROGRAM REGIONALNY
NARODOWA STRATEGIA SPÓJNOŚCI



Projekt współfinansowany przez Unię Europejską z Europejskiego Funduszu Rozwoju Regionalnego oraz z budżetu państwa.

