

Lateral element - UMK-SE 11,25-1

2970442

<https://www.phoenixcontact.com/pc/products/2970442>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Side element, 11.25 mm wide, without marker groove



Lateral element - UMK-SE 11,25-1

2970442

<https://www.phoenixcontact.com/pc/products/2970442>



Commercial Data

Item number	2970442
Packing unit	50 pc
Minimum order quantity	1 pc
Product Key	ACHDCA
Catalog Page	Page 760 (C-1-2013)
GTIN	4017918087722
Weight per Piece (including packing)	5.497 g
Weight per Piece (excluding packing)	5.497 g
Customs tariff number	85389099
Country of origin	PL

Lateral element - UMK-SE 11,25-1

2970442

<https://www.phoenixcontact.com/pc/products/2970442>




Technical Data

Product properties

Product type	Panel mounting base side part
Type	Lateral element
Housing type	Press-drawn section housings
Housing series	UMK

Dimensions

Dimensional drawing	
Length	11.25 mm

External dimensions

Profile width (external)	77 mm
--------------------------	-------

Internal dimensions

Profile width (internal)	72.2 mm
--------------------------	---------

Material specifications

Color	green
Flammability rating according to UL 94	V2
Housing material	Polyamide


Lateral element - UMK-SE 11,25-1

2970442

<https://www.phoenixcontact.com/pc/products/2970442>



Drawings




Lateral element - UMK-SE 11,25-1

2970442

<https://www.phoenixcontact.com/pc/products/2970442>



Approvals



EAC



UL Recognized

Lateral element - UMK-SE 11,25-1



2970442

<https://www.phoenixcontact.com/pc/products/2970442>

Classifications

ECLASS

ECLASS-9.0	27182701
ECLASS-10.0.1	27182701
ECLASS-11.0	27182701

ETIM

ETIM 8.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Lateral element - UMK-SE 11,25-1

2970442

<https://www.phoenixcontact.com/pc/products/2970442>



Environmental Product Compliance

China RoHS

Environmentally friendly use period: unlimited = EFUP-e

No hazardous substances above threshold values

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com