



Cotton Braided HDMI Cable

HDMI UHD cable

More than Real

Real 4K

4K Picture	3D Visuals	Wide Compatibility	Various Mode
---------------	---------------	-----------------------	-----------------

Almost Tangible 3D

4K picture quality with 3D visual effects,
vivid content is ready to come out



3D



4K



Note: All data are from Vention Lab

Smoother than Your Detection

60Hz, indulged in high refresh rate games or movies



Note: All data are from Vention Lab

Universal Compatibility

Connect to projector, HD TV, etc., for devices with standard HDMI interface



Signal Source



Computer



Smart box



PS3/4

...

Display Devices



TV



Monitor



Projector

...


Smart Box **Connect with TV**

Large screen with more immersive experience



PC Connect to Projector

Convenient for business demonstration




Audio and Video Simultaneous Output

Stable transmission and convenient



No Splash and Ghosting

Premium clad-copper wire with multiple shielding provide better anti-interference ability



Note: The internal structure is a rendering, please refer to the actual product

Craftsmanship



Gold-plated interface
durable in swapping, anti-oxidant

PVC+cotton braided
Stretch resistance

Zinc alloy shell
Sturdy, good heat dissipation



More function for Your Exploration

01

Mirror mode

Enjoy same picture
in a larger screen



02

Extension mode

Show different image,
work as well as play



03

Game interaction

PS3/4 connect to TV
More exciting gaming



HDCP Standard Protocol Protection


Vention is a member of the HDMI Association and is compliant with the HDCP standard protocol, ensuring that its genuine content can be used legally



Note: Without the protection of HDCP protocol, the picture quality of mirror mode will be interfered and lowered for content protection

Product Parameters

Brand:	Vention
Name:	Cotton Braided HDMI Cable
Model:	AABI
Color:	Silver Gray
Resolution:	4K*2K@60Hz
Conductor:	Clad-copper
Shell:	Aluminum Alloy
Shielding:	Aluminum Foil
Jacket:	Cotton Braided+PVC
OD:	7.0mm
Length:	0.75m-15m
Warranty:	1 Year
Packing:	Kraft Box+Color Box



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance



Length	Art.No.	EAN Code
0.75m	AABIE	6922794731080
1m	AABIF	6922794731097
1.5m	AABIG	6922794731103
2m	AABIH	6922794731110
3m	AABII	6922794731127
5m	AABIJ	6922794731134
8m	AABIK	6922794731141
10m	AABIL	6922794731158



Package Contents

Cotton Braided HDMI Cable

Packaging Information

Packing Dimension	cm
Packing Weight	kg
Carton Dimension	48*29*30cm
Carton Qty	61pcs(0.75m,1m), 38pcs(1.5m), 56pcs(2m),17pcs(3m,5m)
Carton Weight	9kgs(0.75m-1.5m), 11kgs(2m), 6.8kgs(3m), 10.3kgs(5m)
Package	PE Bag(0.75m-5m), Color box(8m,10m)