



CAT6 UTP Patch Cable



Universal Compatibility

//For all devices with RJ45 network cable interface//



Desktop



Laptop



Router



Switch



TV




TV Box



Digital printer



More




Home



Office



Internet Cafe




Hotel

Gigabit Transmission

1000Mbps
transfer rate, work more efficiently

Note: All data are from Vention Lab



1000Mbps

Safer and Stable Network

Twisted pair structure, reduce interference
cope with network environments such
as home and office easily



Smoother Game

Never miss
one critical moment in game



Stable Streaming

Watch TV shows online
with smooth connection



Four Upgrades

Upgrade 1

Cross Frame Structure


Isolated 4 pairs of twisted pair
stable and anti-interference

PVC jacket

Copper clad
aluminum
conductor

Cross frame


Note: The internal structure is a rendering
please refer to the actual product



Upgrade 2

Bold Conductor Twisted Pair Structure

26AWG copper clad aluminum conductor
faster internet speed



250MHz



1000Mbps

Note: The internal structure is a rendering
please refer to the actual product

Upgrade 3

Gold-plated Brass Contacts

Strongly enhance
transmission speed



Three-pronged chip

Note: The internal structure is a rendering
please refer to the actual product

Upgrade 4

PVC Jacket



Wear-resistant

Anti-stretch

Water-proof

Note: The internal structure is a rendering
please refer to the actual product

Multiple Lengths

0.5m to 5m, suit for different environments

0.5m



3m



5m



Product Parameters

Brand: Vention

Name: Cat.6 UTP Patch Cable

Model: IBEL

Color: Blue

Interface: RJ45

Connector Chips Technics: Three-pronged Chip/Gold-plated Brass

Cross frame: Yes

Transmission standard: Cat.6

Transmission Speed: 1000Mbps

Transfer bandwidth: 250MHz

Conductor: Copper Clad Aluminum

Shell: PC

Jacket: PVC

Shielding: UTP

AWG: 26AWG (7*0.16mm)

OD: 5.5mm

Length: 0.5m/1m/1.5m/2m/3m/5m

Warranty: 1 Year

Packing: PE Bag




Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance



Note: Packing difference exists for different meters or batches.
The photo is for reference only

Length	Art.No.	EAN Code
0.5m	IBELD	6922794748361
1m	IBELF	6922794748378
1.5m	IBELG	6922794748385
2m	IBELH	6922794748392
3m	IBELI	6922794748408
5m	IBELJ	6922794748415



Package Contents

CAT6 UTP Patch Cable

Packaging Information

Packing Dimension	cm
Packing Weight	kg
Carton Dimension	48*29*30cm
Carton Qty	250pcs(0.5m), 200pcs(1m), 150pcs(1.5m), 120pcs(2m), 100pcs(3m), 60pcs(5m)
Carton Weight	8kgs(0.5m-2m), 9.35kgs(3m), 8.86(5m)
Package	PE Bag