



USB 2.0 C Male Right Angle to C Male 5A Cable

Right Angle Interface

Ergonomic design to fit hand

90°

interface cable

10mm

interface length

Note: All data are from Vention Lab



PD100W/5A

USB-C

Right Angle Cable

Designed for mobile gamer



Right angle
design

Huawei FCP/
Qualcomm QC4.0

E-Marker
chip

PD100W Fast Charge



Around **2** Hours full of:
MacBook Pro 2018

Around **2.4** Hours full of:
iPad Pro 11"

Around **2.5** Hours full of:
Nintendo Switch

Note: All data are from Vention Lab




E-Marker Safety Chip

Ensures a well-protected charging environment



Support Samsung/ Huawei Fast Charge

5A(MAX) high current, compatible with
mainstream fast charge protocols



100% 103 min
Full of Huawei P40



100% 75 min
Full of Xiaomi
10 Pro

Note: All data are from Vention Lab

Multiple Shielding Technologies

30/21AWG bold tinned copper conductor




Applicable USB-C Devices

	Laptop	Cellphone
Apple	MacBook12", MacBook Pro 2019 Mac Mini, MacBook Air 2020	Huawei Nova5/6/7 Mate20/30, Mate20/30 Pro Mate20/30 RS P20/30/40 P20/30/40 Pro
Huawei	MateBook, MateBook X/E MateBook 13/14	
Honor	MagicBook, MagicBook 2019	
Xiaomi	Air12.5"/13.3", GTX version 15.6" Xiaomi game book 8 generation	
HP	Pavilion x2, Spectre 13 EliteBook Folio G1, Envy 13 Shadow Wizard 4 Pro	Honor 30, 30S, V30 V20, Magic2 Note 10, V10
ASUS	Ling Yao 3, Ling Yao 3 Pro Ling Yao X series, U306, U321 U4100UN, U5100UQ, ROG	Microsoft Microsoft 950XL Microsoft 950
Dell	XPS13/15, Latitude 5285, G+C22 G3/G5/G7, Lingyue 5000/7000	Xiaomi 9/10 Pro, 9/10 8/9se, 8, 8 Lite Redmi Note7 Redmi K20/K30
Lenovo	Xiaoxin Air 12", Yoga5/6 Pro ThinkPad_X1 Carbon 2017 Saver Y7000/Y7000P/Y9000K	
SAMSUNG	NoteBook series GalaxyBook series	LG G5, V300L
Google	ChromeBook Pixels PixelBook Pen	Samsung S10, S10+, S10e A9s, A9 Stat Note8/9/10
Razer	Blade Stealth Spirit Blade Spirit Blade Sneak Edition	
Microsoft	Surface Book 2, Surface GO	Meizu 16/17th, X8
HTC	HTC 10	vivo Z5, iQOO, X27
Tablet	Apple iPad Pro 2018/2020	OPPO R17 Pro
	Huawei MediaPad M5	Smartisan Nut Pro 2S
	Xiaomi MI PAD 4	BlackShark BlackShark 2
Game console	Nintendo Switch	
More USB-C models will be continuously updated ...		

Enhanced Cable Material

Tough TPE jacket covered with nylon braided mesh



Extra long tail
Anti-breakage

Fast Data Transmission

Standard USB2.0 interface

480Mbps

1G/30seconds



Note: All data are from Vention Lab

Multiple Lengths

Meet different needs

0.5m

Easy for carrying around



1-1.5m

Daily charging use



2m

Charging as well as watching movie



Product Parameters

Brand: Vention	Shielding: Aluminum Foil+Metal
Name: USB 2.0 C Male to C Male Right Angle Cable 5A	Braided
Model: TAKH	Jacket: TPE+Nylon Braided
Color: Gray	AWG: 21+30AWG
Interface: USB 2.0-C Male Right Angle/	OD: 4.1mm
USB 2.0-C Male	Length: 0.5/1/1.5/2m
Interface Technics: Nickel-plated	Rated Input: 5A
Transmission Rate: 480Mbps	Power Supply: PD100W (MAX)
	(20V/5A)
Conductor: Tinned-copper	Warranty: 1 Year
Shell: Aluminum Alloy	Packing: PE Bag
Chip: E-Marker	



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance



Note: Packing difference exists for different meters or batches
The photo is for reference only

