


橡膠腳墊 RUBBER FOOT


用途：背膠式，可快速將腳墊固定於機殼，黏性佳、不脫落。



- Material: Rubber
- Color: Black
- Unit: mm




Part No.	A	B
RF-004	9.9	3.8
RF14-5A	14.0	5.0
RF27-7AC-1	27.8	7.4



Part No.
RF18-5A




- Material: Rubber/Silicon Rubber
- Color: Black
- Unit: mm




Part No.	A	B	C
RF5.8-4A	5.8	5.5	4.0
RF8-3.5	8.0	7.7	3.5
RF8.2-5	8.2	7.6	5.0
RF9-3.5	9.0	8.2	3.5
RF9.7-4.2A	9.7	9.3	4.2
RF15.5-5A	15.4	14.8	5.1
RF19-4A7	19.05	18.05	4.06
RF22.8-5	22.8	22.4	5.0
RF22-8.8	22.0	21.0	8.8
RF22-5	22.0	21.0	5.0



- Material: Rubber/Silicon Rubber
- Color: Black
- Unit: mm
- Other Materials Available: EPDM



Part No.	A	B	C
RF6-5	6.0	5.0	5.0
RF7-4.2A	7.0	6.5	4.2
RF7-3.2A	7.0	6.6	3.2
RF8-6.5A	8.0	7.2	6.5
RF-1094A	10.0	9.0	9.4
RF-003	10.0	9.5	4.2
RF-030	10.0	9.5	8.0
RF-1055	10.0	9.7	5.5
RF-009	10.8	10.2	3.0
RF11-5	11.0	9.6	5.0
RF-011	11.0	10.5	5.0
RF11-3.2A	11.3	10.7	3.2
RF12-27A	12.0	11.6	2.7
★ RF12.7-6.2A	12.7	10.0	6.2
RF-039	11.9	11.2	6.4



[RF7-4.2A, RF8-6.5A, RF12.7-6.2A, RF17-11A]

Part No.	A	B	C
RF-015	12.0	11.2	5.1
RF-019	12.0	9.5	4.0
RF-019A	12.7	10.0	3.8
RF-032	12.7	11.5	4.0
RF-005	13.0	11.4	5.0
RF-012	13.0	12.2	4.5
RF15-11A	15.0	13.5	11.0
RF17-11A	17.0	13.25	11.0
RF-007	19.0	17.0	7.2
RF-020	19.0	15.8	4.2
RF20-5	19.8	18.0	5.0
RF-008	20.0	19.0	6.0
RF24-8	24.0	20.0	8.0