

Special tools for lubrication service

12005 Strap wrenches

- for oil filters etc., up to 180 mm $\varnothing$
- non-slip rubber cloth tape, 22 mm width



Code	No	L mm	$\Delta\Delta$ g	
76500001	12005	236	264	1
79150001	12005/1 ¹⁾	600	69	1

¹⁾ spare strap

12007 Oil filter wrenches

- adjustable for diameters 80-110 mm
- hardened anti-slip cams ensure safety during use



Code	No	L mm	$\Delta\Delta$ g	
76521001	12007/1 ¹⁾	150	226	1
76521002	12007/2 ²⁾	240	319	1

¹⁾ with 1/2" $\odot$

²⁾ with lever handle

10765-12 Hexagon key wrench

- Fiat-No A 5013
- for hexagon socket
- long
- 12 mm
- for oil drain plug on engine, gearbox and rear axle



Code	Type	$\Delta\Delta$ g	
43210012	Fiat	287	5

1058 Oil service spanner

- bent
- 8 and 10 mm outside square
- for drain plugs on sump, gearbox, differential



Code	Type	$\Delta\Delta$ g	
44730810	Peugeot, Renault	315	5

1015 Oil filter claw

- for loosening of oil filters on cars



Code	$\odot$ "	Clamp. width mm	total height mm	length of claws mm	$\Delta\Delta$ g	
74620002	3/8	68-120	65	50	530	1

3045 Special socket

- for oil filters
- 74 mm
- 14-point
- 10 mm dia. bore and outside hexagon 22 mm $\varnothing$



Code	total height mm	$\Delta\Delta$ g	
74370001	52	131	1

3046 Special sockets

- for fitting and removing oil filter covers when changing oil filter cartridges



Code	$\odot$ mm	$\odot$ "	Type	$\Delta\Delta$ g	
02111032	32	3/8	e.g. Audi, MAN, Vauxhall Astra, Corsa, VW Passat	130	1
02111036	36	3/8	e.g. BMW, Mercedes-Benz cars, 100 D Transporter, MAN, Vauxhall Vectra B DI 16V, VW Lupo 1.2 TDI, model year 99	160	1

54-14 INEX socket

- for hexagon socket head screws, 14 mm
- 1/2" $\odot$ -drive
- for use on oil drain plug



Code	Type	$\Delta\Delta$ g	
03050014	Mercedes-Benz	135	5

1054-13 INEX sockets

- for hexagon socket head screws, 13 mm
- length 70 mm
- 1/2" $\odot$ -drive
- for oil drain plug on engine



Code	Type	$\Delta\Delta$ g	
03150713	Lancia	130	5