

4691/7 DRALL⁺ set of screwdrivers

Set of 7 **DRALL⁺** screwdrivers
 content:
 ⊖ 4620:
 size 1 (0.6 x 3.5 x 75 mm)
 size 2 (0.8 x 4.0 x 100 mm)
 size 3 (1.0 x 5.5 x 125 mm)
 size 4 (1.2 x 6.5 x 150 mm)
 ⊖ 4628: size 1 (0.4 x 2.5 x 60 mm)
 ⊕ 4630: PH1; PH2



Code	g	
96 46 91 15	580	1

4692/8 DRALL⁺ set of screwdrivers

Set of 8 **DRALL⁺** screwdrivers
 Content:
 ⊖ 4620:
 size 1 (0.6 x 3.5 x 75 mm)
 size 2 (0.8 x 4.0 x 100 mm)
 size 3 (1.0 x 5.5 x 125 mm)
 size 4 (1.2 x 6.5 x 150 mm)
 size 5 (1.6 x 8.0 x 175 mm)
 ⊕ 4630: PH1; PH2; PH3



Code	g	
96 46 92 15	840	1

4693/9 DRALL⁺ set of screwdrivers

Set of 9 **DRALL⁺** screwdrivers
 Content:
 ⊖ 4622:
 size 1 (1.0 x 5.5 x 100 mm)
 size 2 (1.2 x 6.5 x 125 mm)
 size 3 (1.2 x 8.0 x 150 mm)
 size 4 (1.6 x 10.0 x 175 mm)
 ⊖ 4628: size 1 (0.4 x 2.5 x 60 mm)
 ⊕ 4632: PH1; PH2
 ⊖ 4724: size 2 (1.0 x 5.5 x 25 mm)
 ⊕ 4734: PH2



Code	g	
96 46 93 15	950	1

4696/6 DRALL⁺ set of screwdrivers

Set of 6 **DRALL⁺** screwdrivers
 with an impact cap
 Content:
 ⊖ 4622SK:
 size 1 (0.8 x 4.0 x 90 mm)
 size 2 (1.0 x 5.5 x 100 mm)
 size 3 (1.2 x 6.5 x 125 mm)
 size 4 (1.2 x 8.0 x 150 mm)
 ⊕ 4632SK: PH1; PH2



Code	g	
96 46 96 15	870	1

4697/8 DRALL⁺ set of screwdrivers

Set of 8 **DRALL⁺** screwdrivers
 Content:
 ⊖ 4620:
 size 1 (0.6 x 3.5 x 75 mm)
 size 2 (0.8 x 4.0 x 100 mm)
 ⊖ 4622:
 size 1 (1.0 x 5.5 x 100 mm)
 size 2 (1.2 x 6.5 x 125 mm)
 size 3 (1.2 x 8.0 x 150 mm)
 ⊕ 4732: PH1; PH2; PH3



Code	g	
96 46 97 15	930	1

4694/9 DRALL⁺ set of TORX[®] screwdrivers

Set of 9 **DRALL⁺** screwdrivers
 for TORX[®] screws
 Content:
 ⊕ 4650: T8, T9, T10, T15, T20, T25,
 T27, T30, T40



Code	g	
96 46 94 15	730	1

4699/9 DRALL⁺ set of TORX[®] screwdrivers


Set of 9 **DRALL⁺** screwdrivers
 for TORX[®] screws
 (TORX[®] TAMPER RESISTANT).
 Content:
 ⊕ 4656: T8, T9, T10, T15, T20, T25,
 T27, T30, T40
 (with hollow point)



Code	g	
96 46 99 15	740	1

TCS 4620/4630

- 175 x 350 x 35 mm
- 7 pieces



Code	g
96 83 82 78	590

No	Content
4620	size 1 (0.6 x 3.5 x 75 mm) size 2 (0.8 x 4.0 x 100 mm) size 3 (1.0 x 5.5 x 125 mm) size 4 (1.2 x 6.5 x 150 mm)
4630	PH1; PH2; PH3