



Cat.6 SFTP Extension Patch Cable

Cat.6 SFTP Extension Patch Cable

Solve the problem that the network
cable is not long enough



1000Mbps
250MHz

Oxygen-free copper
Twisted pairs

Aluminum foil
Metal mesh

Bold wire diameter
High elastic jacket

Extended at Will

Easily solve the problem that the network cable is not long enough when embedded



Application 1



Application 2

1000Mbps Transfer Rate

Vastly improve your Lan throughput

1000Mbps **250**MHz



Gaming stable



Download fast



HD video streaming



Five Upgrades

Upgrade 1


Bold Copper Conductor Twisted Pairs

26

AWG
oxygen-free
copper


4pairs

of twisted
pair structure




Upgrade 2

Double Shield Stable Network



Upgrade 3

Wear-resistant RJ45 Plug 10000 Times Swapping Test




Note: All data are from Vention Lab.

Upgrade 4

Gold-plated Contacts

Wear-resistant and strongly enhance
transmission speed



Upgrade 5

Anti-fracture More Flexible




PVC

Tough PVC jacket

6.2mm


bold wire diameter

Multiple Devices and Scenes



FLUKE Networks Test

Meet the Cat.6 network cable standards



Multiple Length

0.5m



10m



Product Parameters

Brand: Vention	Conductor: Oxygen-free Copper
Name: Cat.6 SFTP Extension Patch Cable	Shielding: Aluminum Foil+Metal Mesh
Model: IBL	Jacket: PVC
Color: Black	AWG: 26AWG
Interface: RJ45	OD: 6.2mm
Transmission Rate: 1000Mbps	Length: 0.5/1/1.5/2/3/5/8/10m
Transmission Bandwidth: 250MHz	Warranty: 1 Year
Interface Technics: PC	Packing: PE Bag
Shield Shell: Gold-plated Copper Shell Male, Nickel-plated Copper Shell Female	
Connector Chips Technics: Phosphor Bronze Gold-plated Trigeminal Chip	



Note: Packing difference exists for different meters or batches.
The photo is for reference only.

Length	Art.No.	EAN Code
0.5m	IBLBD	6922794745674
1m	IBLBF	6922794745681
1.5m	IBLBG	6922794745698
2m	IBLBH	6922794745704
3m	IBLBI	6922794745711
5m	IBLBJ	6922794745728
8m	IBLBK	6922794745735
10m	IBLBL	6922794745742



Package Contents

Cat.6 SFTP Extension Patch Cable

Packaging Information

Packing Dimension	cm
Packing Weight	kg
Carton Dimension	48*29*30
Carton Qty	150pcs(0.5m), 100pcs(1m,1.5m),80pcs(2m),50pcs(3m,5m), 25pcs(8m,10m)
Carton Weight	6.5kgs(0.5m,1m), 8kgs(2m,3m),9kgs(1.5m), 10kgs(5m,10m)
Package	PE Bag