



CAT6a UTP Patch Cord Cable

10Gbps Slim & Portable

Cat.6A Patch Cable Slim Type



High
Speed

Convenient
Cabling

Stable
Transmission

Slim Type For Convenient Cabling

2.8mm flexible cable Designed for cabling and traveling

ULTRA-SLIM **2.8**mm



Note: All data are from Vention lab.

Better Network Performance



Stable
Gaming



HD Video
Streaming



Fast
Download



10Gbps Transmission Rate

Vastly improve network throughput

Transmission rate **10Gbps**

Bandwidth **500MHz**



Note: All data are from Vention lab.


100% Signal Transmission

4 shielded twisted pairs Oxygen-free copper Conductor

Nylon Wire for
Stretch Resistance

32AWG Oxygen-free
Copper Conductor

PVC Jacket



VENTION

24K Gold-plated Contacts

Wear resistance & faster transmission



Trigeminal Chip Gold-plated Contacts

High Durable Quality

Stretch resistance with slim & flexibel cable



Universal Compatibility



Desktop



Laptop



Set top box



HUB



Router



Switcher



ADSL



MODEM



OPTICAL MODEM

Universal Scenes



Office



Home



Travel



Hotel

Product Parameters

Brand: Vention	Conductor: Oxygen-free Copper
Name: Cat.6A UTP Patch Cable Slim Type	Jacket: PVC
Model: IBI	AWG: 32AWG
Color: Black	OD: 2.8mm
Connector: RJ45	Length: 0.5m-10m
Version: Cat. 6A	Warranty: 1Year
Interface: Gold-plated	Packing: PE Bag

Note:All data are from Vention lab.



Note: Sizes are manually measured. There might be slight tolerance.

Multiple Lengths

Short meters: 0.5m



Long meters: 10m



Note: Package differs on lengths and batches, please take the actual packing as the standard.

Length	Art.No.	EAN Code
0.5m	IBIBD	6922794742932
1m	IBIBF	6922794742949
1.5m	IBIBG	6922794742956
2m	IBIBH	6922794742963
3m	IBIBI	6922794742970
5m	IBIBJ	6922794742987



Package Contents

CAT6a UTP Patch Cord Cable

Packaging Information

Packing Dimension	cm
Packing Weight	kg
Carton Dimension	48*29*30
Carton Qty	300pcs(0.5m), 260pcs(1m), 250pcs(1.5m,2m,3m) , 140pcs(5m)
Carton Weight	5.5kgs(0.5m), 6.5kgs(1m), 7.2kgs(1.5m), 8.8kgs(2m,5m)),11kgs(3m)
Package	PE Bag