



USB-C to VGA Converter

For larger screen extension

USB-C to VGA HD Converter



Screen extension
Office/study



HD vision
1080P@60Hz



Two mode
Mirror/extension



Driver free
Plug&Play

Movie-watching 

Phone Connect to TV

Improved movie experience via larger screen



Laptop Connect to Projector

Enhanced presentation/domenstration efficiency



Game 

Phone Connect to Monitor

Screen synchronization, detect more game details



Study 


iPad Pro Connect to TV

Doing online course via larger screen, relief eye stress



High Performance and Stable

RTD2169D high performance chip, avoid ghosting
and splash



Note: the internal circuit/chip is a rendering, please refer to the actual product

Driver Free for Mainstream OS

Plug and Play for Windows, Mac OS, Vista, etc.



Windows10



Windows8



Windows7



WindowsXP



Mac OS



Vista



Linux



Android OS



iOS

Designed for USB-C Interface

Laptop



MacBook



Lenovo



MateBook



HP



ASUS



Xiaomi



Dell



Other devices...

Tablet



iPad



MatePad



Surface



Other devices...

Mobile Phone



Huawei Mate40
Mate 40 Pro/20 X



Huawei P40
P40 Pro



Samsung S20/S10+
Note20



OPPO Reno 3
R17 Pro



Smartisan R1
Pro 2S



Other devices...



Part of Supported Models

Laptop

Apple	MacBook12", MacBook Pro2016/2017/2018/2019, Mac Mini, MacBook Air 2018/2019/2020
Huawei	MateBook, MateBook X, MateBook X Pro, MateBook X Pro 2019, MateBook E, MateBook E 2019, MateBook 13, MateBook 14
Honor	MagicBook, MagicBook 2019
Xiaomi	Air12.5"/ 13.3", Pro15.6", GTX version 15.6", Xiaomi game book 8 generation
HP	Pavilion x2, Spectre 13, EliteBook Folio G1, Elite Book1050 G1, Envy 13, Shadow Wizard 4 Pro
ASUS	Ling Yao 3, Ling Yao 3 Pro, Ling Yao X series, U306, U321, U4100UN, U5100UQ, ROG
Dell	XPS13/15, Latitude 5285, G+C22, G3/G5/G7, Lingyue 5000/7000
Lenovo	Xiaoxin Air 12", Yoga5 Pro, Yoga6 Pro, Yoga 900 13", Miix 720, ThinkPad_X1 Carbon 2017, Saver Y7000/Y7000P/Y9000K
SAMSUNG	NoteBook series, GalaxyBook series
Google	ChromeBook Pixels, PixelBook Pen
Razer	Blade Stealth Spirit Blade, Spirit Blade Sneak Edition
Microsoft	Surface Book 2, Surface GO
HTC	HTC 10

Mobile Phone

SAMSUNG

Note8, Note9, S8/S8+, S9/S9+, S10/S10+, S20, Note10, Note10+

Huawei

Mate10, Mate10 Pro, Mate20, Mate20 Pro, Mate20 X, Mate20 RS, P20, P20 Pro, Mate X, P30, P30 Pro, Mate30, Mate30 Pro, P40, P40Pro

Microsoft

Microsoft 950XL, Microsoft 950

LG

G5, V300L

Smartisan

Nut R1, Nut Pro 2S

OPPO

R17 Pro, Reno 10x Zoom

BlackShark

BlackShark 2

iPad

Apple

iPad Pro 2018/2020

Huawei

MatePad 10.4/10.8", MatePad Pro, MediaPad M6

Microsoft

Surface Pro7, Surface Go/Go2, Surface Book 2

More USB-C models will be continuously updated
Note: not applicable to Xiaomi / Redmi USB-C mobile phones

Two Modes, Two Functions

01

Mirror mode

Show same images in two screens



02

Extension mode

Show different image work as well as play



Product Parameters

Brand: Vention	Shell: Aluminum Alloy
Name: USB-C to VGA Converter Aluminum Alloy Type	
Model: TDFHB	Chip: RTD2169D
Color: Gray	Jacket: TPE
Interface: USB-C Male/VGA Female	AWG: 34AWG+26AWG
Interface Technics: Nickel-plated	OD: 4.2mm
Resolution: 1080P@60Hz	Length: 0.15m
Conductor: Tinned-copper	Warranty: 1 Year
Shielding: Aluminum Foil+Metal Braided+GND	Packing: PE Bag



Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.

Length	Art.No.	EAN Code
0.15m	TDFHB	6922794754690



Package Contents

USB-C to VGA Converter

Packaging Information

Packing Dimension	cm
Packing Weight	kg
Carton Dimension	40*30*30
Carton Qty	60pcs
Carton Weight	5kgs
Package	Color Box