

# Technical data sheet

CU480MC

USB-C TO DP Cable 8K@60Hz Aluminum Shell



Version: A/0

## 【Product Picture】



## 【Product Description】

USB Type C to DP/M cable 8K@60Hz, Aluminum Shell

## 【Interface description】

Connector 1: USB type C Male

Connector 2: Display port Male

DP : Max 8K@60Hz/4k@120Hz/2K@144Hz

Length: 1.8m

## 【Compatibility Test】

|              |           |                                                                                                                                                              |
|--------------|-----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Mobile phone | Samsung   | S8/S8 plus/ S9/S9 plus/ S10/S10 plus /S20/S20 ultra/21/21 ultra/Note8/Note9/note10/note 20                                                                   |
|              | Huawei    | Mate (10 / 10 Pro/ 20/20 Pro/20 RS/ Mate 20 X / 30/30Pro/40/40 Pro ) P20/P20 Pro/P30/P30 Pro/P40/P40 Pro Nava 5/5i/5 Pro/5i Pro honor Note 10 / Note V20 etc |
|              | smartisan | R1Pro2S etc                                                                                                                                                  |
|              | OPPO      | R17 PRO etc                                                                                                                                                  |
|              | HTC       | U11 etc                                                                                                                                                      |
|              | LG        | G5 G6 etc                                                                                                                                                    |

# Technical data sheet

CU480MC

USB-C TO DP Cable 8K@60Hz Aluminum Shell

|                 |           |                                                                                                                                                                               |
|-----------------|-----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| PC              | Apple     | 12 inch Macbook (2015-2017) / Macbook A1534(2017) / iMac (2017-2021) / iMac pro(2017-2021) / Mac mini (2018) /Macbook Pro( 2016-2021)/ Mac mini / MacBook Air( 2018-2021) etc |
|                 | Huawei    | MateBook x/MateBook xPro/MateBook E/MateBook/MateBook 13/MateBook 14/MateBook D etc                                                                                           |
|                 | Xiaomi    | Air 12.5/13.3 inch、Pro 15.6 inch、Xiaomi game book/RedmiBook 14/ Xiaomi pro 2019/ xiaomi ruby 2019/ xiaomi air 2019                                                            |
|                 | Asus      | Lingyao3/ 3 Pro/ X series/ NB-ZenBook 3U、U306、U321 series、U4100ROG series,UX501Acer Swift7HP Elite X2MSI GS40Dell XPS13 etc                                                   |
|                 | Lenovo    | Yoga/Yoga5 Pro/ Yoga6 Pro/ Yoga900 13 inch/ ThinkPad X1 Carbon 2017、Mix720/Air 13 Pro/ Idea pad 720s /ThinkPad 13/etc                                                         |
|                 | HP        | Jingling4 Pro / Pavilion X2、EliteBook Folio G1/840 G5/ SPECTRE 13 etc                                                                                                         |
|                 | Samsung   | NoteBook series/ Galaxy series etc                                                                                                                                            |
|                 | Dell      | G3/G5/G7 series/Lingyue5000/ Lingyue700/XPS13/ XPS15 etc                                                                                                                      |
|                 | Google    | ChromeBook Pixels、PixlBook Pen etc                                                                                                                                            |
|                 | Razer     | Blade Stealth etc                                                                                                                                                             |
|                 | Microsoft | Surface Book 2 /Surface Go etc                                                                                                                                                |
| Tablet          | Apple     | 2018 Apple iPad Pro 11 inch /The 3th iPad Pro 12.9 inch                                                                                                                       |
|                 | Huawei    | M5/M6/Mate book e                                                                                                                                                             |
|                 | Samsung   | Galaxy Tab S7/S6/Tab S5e/ Tab A10.5/ Tab S4 / TabS3 9.7 / Galaxy Book                                                                                                         |
| Nintendo Switch | Switch    | Switch<br>2017/2018/2019/2020/2021                                                                                                                                            |

## 【Attention】

- 1.System environment compatible with: Windows/Linux/Mac OS/Android.
- 2.If the device is forcibly removed, it may cause data or disk errors, damage and loss, please follow the specifications for device removal operation.
3. Do not place the product in an environment where corrosive substances are present.
4. Do not place the product and accessories in apparatus with strong electromagnetic fields and keep away from magnetic devices.

# Technical data sheet

CU480MC

USB-C TO DP Cable 8K@60Hz Aluminum Shell

---

5. Do not hit, throw or pinch the product, avoid dropping, crushing or bending the product.
6. Do not place the product in high temperature, low temperature, humid, dusty or exposed to sunlight for a long period of time, and keep away from fire sources.