



VGA(3+9) Male to Male Cable

VGA 3+9 Ferrite Ring Cable

Signal non-distortion in 30m transmission



1080P
HD

Gold-plated
plug

CCA+BC
conductor

Double ring
shielding

Computer Connect to Monitor

Enjoy the exciting vision with high HD picture



Support Resolution Up to 1080P

Including 800×600(SVGA), 1024×768(XGA)
1600×1200(UXGA), 1080P(Full HD), 1920×1200(WUXGA)
and up for high resolution LCD and LED monitors




* All data are from Vention laboratory

Application Demonstration

Two modes, meet different needs

Mirror Mode




Ferrite Ring For Anti-interference

Against EMI and RFI



Length	AWG	Ferrite Ring	Resolution	OD
1-5m	30AWG+24AWG	Dual Ferrite Rings	1080P	6.0mm
8-30m	28AWG+24AWG	Dual Ferrite Rings	1080P	8.0mm

Extended Mode



Gold-plated Connectors

Anti-oxidation, no rust, reduce transmission loss




Environmental PVC Jacket

Soft and flexible, ensure longer service life




Internal Structure Display

CCA+BC conductors, dual aluminum foil+metal braided shielding, ensure stable transmission and clear picture



SR Tail Reinforcement

Not easy to break when used in a small space for a long time




SR Tail Reinforcement

Widely Compatible

Suitable for all VGA port devices

Input devices



HDTV



Projector



Monitor




Output devices



DVD



Host



Set-top box



Laptop

Product Parameters

Brand	Vention
Name	VGA Cable(3+9)
Model	DAD
Color	Black
Type	VGA Male
Connector	Gold plated
Conductor	CCA+BC
Jacket	PVC
Shielding	Aluminum Foil+Metal Braided
OD	6mm(1-5m),8mm(8-30m)
Length	1m-30m
AWG	30AWG+24AWG(1-5m)/28AWG+24AWG(8-30m)
Warranty:	One year
Package	PE bag(1m-5m)/Kraft box(8m-30m)

* All data are from Vention laboratory



PE bag (Below 5 meters)



Kraft box (Above 8meters)

Length	Art.No.	EAN Code
1m	DADBF	6922794733022
1.5m	DADBG	6922794733039
2m	DADBH	6922794733046
3m	DADBI	6922794733053
5m	DADBJ	6922794733060
8m	DADBK	6922794733077
10m	DADBL	6922794733084
15m	DADBN	6922794733107
20m	DADBQ	6922794733114
25m	DADBS	6922794733121



Package Contents

VGA(3+9) Male to Male Cable

Packaging Information

Packing Dimension	cm
Packing Weight	kg
Carton Dimension	48*29*30cm(1m-5m), 46*40*40(8m), 52*46.5*24.5(10m-25m)
Carton Qty	100pcs(1m), 60pcs(1.5m-2m), 50pcs(3m), 35pcs(5m), 28pcs(8m-10m), 12pcs(15m-25m)
Carton Weight	13kgs(1m), 9kgs(1.5m,2m), 11.2kgs(3m,5m), 18kgs(8m),22kgs(10m-25m)
Package	Color Box

www.ventioncable.com