



PRODUCT-DETAILS

TY300-40-39

TYFAST 3,6X290MM NATURAL HEAT STAB.



General Information

Extended Product Type	TY300-40-39
Product ID	7TCG054360R0248
EAN	5414363063902
Catalog Description	TYFAST 3,6X290MM NATURAL HEAT STAB.
Long Description	Cable Tie, Heat Stabilized Natural Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 289.56mm (11.4 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.168mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Bulk Pack

Ordering

EAN	5414363063902
UPC	786210840567
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.14 in 3.556 mm
Product Net Depth / Length	11.4 in 289.56 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	14 in 356 mm
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	14 in 356 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	15.4 in 391 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23.6 in 599 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	3 in 76.2 mm
Color	Natural
Effective Date	20020509
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	OTHER ARTICLES OF PLASTICS
Product Type	Heat Stabilized
Standards	UL E49405
Tensile Strength	40 lb 180 N
Thickness	0.046 in 1.17 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY300-40-39
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY300-40-39

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

