



## PRODUCT-DETAILS

# TY300-40-6

## CBL TIE 40LB 11IN BLUE NYLON



### General Information

|                       |                                                                                                                                                                                                                                                                                                                                        |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type | TY300-40-6                                                                                                                                                                                                                                                                                                                             |
| Product ID            | 7TCG054360R0254                                                                                                                                                                                                                                                                                                                        |
| EAN                   | 5414363063964                                                                                                                                                                                                                                                                                                                          |
| Catalog Description   | CBL TIE 40LB 11IN BLUE NYLON                                                                                                                                                                                                                                                                                                           |
| Long Description      | Cable Tie, Blue Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 289.56mm (11.4 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.168mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Bulk Pack |

### Ordering

|                              |                 |
|------------------------------|-----------------|
| EAN                          | 5414363063964   |
| UPC                          | 786210766560    |
| Replacement Product ID (NEW) | 7TAG009160R0029 |
| Country of Origin            | Hungary (HU)    |
| Customs Tariff Number        | 3926909990      |
| Selling Unit of Measure      | each            |

### Dimensions

|                            |                      |
|----------------------------|----------------------|
| Product Net Width          | 0.14 in<br>3.556 mm  |
| Product Net Depth / Length | 11.4 in<br>289.56 mm |

## Container Information

|                                |                   |
|--------------------------------|-------------------|
| Package Level 1 Units          | 1000 piece        |
| Package Level 1 Width          | 15 in<br>381 mm   |
| Package Level 1 Height         | 4 in<br>102 mm    |
| Package Level 1 Depth / Length | 21 in<br>533 mm   |
| Package Level 2 Units          | 10000 piece       |
| Package Level 2 Width          | 15.4 in<br>391 mm |
| Package Level 2 Height         | 11 in<br>279 mm   |
| Package Level 2 Depth / Length | 23.6 in<br>599 mm |

## Technical UL/CSA

|                                |     |
|--------------------------------|-----|
| Flammability According to UL94 | V-2 |
|--------------------------------|-----|

## Additional Information

|                  |                              |
|------------------|------------------------------|
| Brand / Label    | Catamount                    |
| Bundle Diameter  | 3 in<br>76.2 mm              |
| Color            | Blue                         |
| Effective Date   | 19970904                     |
| Lock Type        | Plastic Pawl                 |
| Material         | Nylon/Polyamide 6.6          |
| Product Name     | CATAMOUNT FASTENING PRODUCTS |
| Product Type     | General Purpose              |
| Standards        | UL E49405                    |
| Tensile Strength | 40 lb<br>180 N               |
| Thickness        | 0.046 in<br>1.17 mm          |

## Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | TY300-40-6      |
| Declaration of Conformity - CE    | 9AKK107492A9843 |
| Instructions and Manuals          | TY300-40-6      |

## Classifications

|                                    |                           |
|------------------------------------|---------------------------|
| ETIM 6                             | EC000046 - Cable tie      |
| ETIM 7                             | EC000046 - Cable tie      |
| ETIM 8                             | EC000046 - Cable tie      |
| UNSPSC                             | 39121703                  |
| WEEE Category                      | Product Not in WEEE Scope |
| IDEA Granular Category Code (IGCC) | 5034 >> Cable ties        |

---

Categories

---

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

