



## PRODUCT-DETAILS

# TYH26M

## CABLE TIE 30LB 11IN GR NYL HEAT STB



### General Information

|                       |                                                                                                                                                                                                                                                                                                                                        |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type | TYH26M                                                                                                                                                                                                                                                                                                                                 |
| Product ID            | 7TCG009590R0007                                                                                                                                                                                                                                                                                                                        |
| EAN                   | 5414363067436                                                                                                                                                                                                                                                                                                                          |
| Catalog Description   | CABLE TIE 30LB 11IN GR NYL HEAT STB                                                                                                                                                                                                                                                                                                    |
| Long Description      | Cable Tie, Heat Stabilized Polyamide (Nylon 6.6) - Greenish Tint for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, Length of 277mm (10.9 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 76mm (2.99 Inches), Tensile Strength Rating of 120 Newtons (27 Pounds) |

### Ordering

|                         |               |
|-------------------------|---------------|
| EAN                     | 5414363067436 |
| UPC                     | 786210514673  |
| Country of Origin       | Hungary (HU)  |
| Customs Tariff Number   | 3926909990    |
| Selling Unit of Measure | each          |

### Container Information

|                        |                   |
|------------------------|-------------------|
| Package Level 1 Units  | 1000 piece        |
| Package Level 2 Units  | 10000 piece       |
| Package Level 2 Width  | 10.2 in<br>259 mm |
| Package Level 2 Height | 13.8 in           |

|                         |         |
|-------------------------|---------|
|                         | 351 mm  |
| Package Level 2 Depth / | 19.7 in |
| Length                  | 500 mm  |

## Technical UL/CSA

|                                |     |
|--------------------------------|-----|
| Flammability According to UL94 | V-2 |
|--------------------------------|-----|

## Additional Information

|                  |                           |
|------------------|---------------------------|
| Brand / Label    | Ty-Rap                    |
| Bundle Diameter  | Max 4.02 in<br>Max 102 mm |
| Color            | Green Tint                |
| Effective Date   | 19980621                  |
| Lock Type        | Stainless Steel Barb      |
| Product Name     | TY-RAP FASTENING          |
| Product Type     | Heat-Stabilized           |
| RoHS Date        | 9AKK108466A3874           |
| Standards        | UL E49405                 |
| Tensile Strength | 27 lb<br>120 N            |
| Thickness        | 0.05 in<br>1.3 mm         |

## Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | TDS000494       |
| Instructions and Manuals          | TYH26M          |
| REACH Declaration                 | 9AKK108466A3877 |
| RoHS Information                  | 9AKK108466A3874 |

## Classifications

|                                    |                           |
|------------------------------------|---------------------------|
| ETIM 6                             | EC000046 - Cable tie      |
| ETIM 7                             | EC000046 - Cable tie      |
| ETIM 8                             | EC000046 - Cable tie      |
| UNSPSC                             | 39121703                  |
| WEEE Category                      | Product Not in WEEE Scope |
| IDEA Granular Category Code (IGCC) | 5034 >> Cable ties        |

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

