



PRODUCT-DETAILS

YRL-10-750-BC

CABLE TIE 7X750MM SS COATD RELEAS



General Information

Extended Product Type	YRL-10-750-BC
Product ID	7TCG009210R0072
EAN	5414363125129
Catalog Description	CABLE TIE 7X750MM SS COATD RELEAS
Long Description	Releasable and Reusable Stainless Steel Cable Tie, Black Polyester Coating for Temperatures up to 150 Degrees Celsius (302 F), Weather and Ultraviolet Resistant, Length of 750mm (29.53 Inches), Width of 10mm (0.39 Inch), Thickness of 0.61mm (0.02 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds)

Ordering

EAN	5414363125129
UPC	786210936215
Country of Origin	India (IN)
Customs Tariff Number	7326908688
Selling Unit of Measure	each

Dimensions

Product Net Width	0.39 in 10 mm
Product Net Depth / Length	29.53 in 750 mm

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	35.8 in 909 mm
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	9.1 in 231 mm
Package Level 2 Units	500 piece
Package Level 2 Width	9.4 in 239 mm
Package Level 2 Height	11.8 in 300 mm
Package Level 2 Depth / Length	36.4 in 925 mm

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	20040806
Lock Type	Stainless Steel Barb
Material	Stainless Steel
Product Name	STAINLESS STEEL CABLE TIE
Product Type	Stainless Steel
RoHS Date	9AKK108466A7851
Tensile Strength	250 lb 1112 N
Thickness	0.02 in 0.61 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	YRL-10-750-BC
Declaration of Conformity - CE	9AKK107492A9838
Instructions and Manuals	YRL-10-750-BC
REACH Declaration	9AKK108466A7850
RoHS Information	9AKK108466A7851

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5045 >> Releasable Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

p