

PRODUCT-DETAILS

YRL-5-230-BC

CABLE TIE 5X230MM SS COATD RELEAS



General Information

Extended Product Type	YRL-5-230-BC
Product ID	7TCG009210R0077
EAN	5414363125037
Catalog Description	CABLE TIE 5X230MM SS COATD RELEAS
Long Description	Releasable and Reusable Stainless Steel Cable Tie, Black Polyester Coating for Temperatures up to 150 Degrees Celsius (302 F), Weather and Ultraviolet Resistant, Length of 230mm (9.1 Inches), Width of 5mm (0.20 Inches), Thickness of 0.61mm (0.02 Inches), Tensile Strength Rating of 334 Newtons (75 pounds)

Ordering

EAN	5414363125037
UPC	786210936079
Country of Origin	India (IN)
Customs Tariff Number	7326908688
Selling Unit of Measure	each

Dimensions

Product Net Width	0.2 in 5 mm
Product Net Depth / Length	9.1 in 230 mm

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	7.5 in 191 mm
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	11.8 in 300 mm
Package Level 2 Units	2500 piece
Package Level 2 Width	12.4 in 315 mm
Package Level 2 Height	10.2 in 259 mm
Package Level 2 Depth / Length	12.6 in 320 mm

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	20040806
Lock Type	Stainless Steel Barb
Material	Stainless Steel
Product Name	STAINLESS STEEL CABLE TIE
Product Type	Stainless Steel
RoHS Date	9AKK108466A7851
Tensile Strength	75 lb 334 N
Thickness	0.02 in 0.61 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	YRL-5-230-BC
Declaration of Conformity - CE	9AKK107492A9838
Instructions and Manuals	YRL-5-230-BC
REACH Declaration	9AKK108466A7850
RoHS Information	9AKK108466A7851

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5045 >> Releasable Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

