


Item name:	VWJK05	Pictures: 
Fabric:	100% polyester 300D PU coated	
Lining:	100% polyester taffeta,190T	
Padding:	100% polyester quilted lining,180gsm	
Reflective fabric:	Backing:100% polyester, with coating (glass micro-beads), 2" cutting, grey color Washing at 40°C cycles 25, dry cleaning cycles 5	
Color:	Hi visibility yellow/Navy; Hi visibility orange/Navy	
Features:	Waterproof taped seams, secure cell phone pocket with velcro, sleeve hem worked with rips cuff inside and concealed hood with drawcord, full length 2 ways zipper in front, covered with button panel and with press button fastening	

Size guide(cm)

	Garment Size (Tol.+3/-2) cm	S	M	L	XL	XXL	XXXL
	A. to fit body length(cm)	156-164	164-172	172-180	180-188	188-196	196-204
	B. to fit chest width(cm)	86-94	94-102	102-110	110-118	118-129	129-141

Washing instruction:	 MAX 25X
Packing:	1pc in polybag with EAN code sticker, 10pcs in each carton. Size: S-M:62*42*34cm, L-XL:66*44*34cm, 2XL-3XL:71*46*34cm

Certification

Fabric:	EN ISO20471:2013; EN343:2003+A1:2007
Reflective Tape:	EN ISO20471:2013

Garment:

EN ISO 20471:2013
+A1:2016



3

Performance class of garment	Class			Classification
Minimum materials	3	2	1	EN ISO 20471:2013+A1:2016 Class 3
Background material(m2)	0.8	0.5	0.14	
Retroreflective material(m2)	0.2	0.13	0.1	

EN343:2003+A1:2007



3
1

Resistance to water penetration	Class			Classification
Test to be made	1	2	3	EN343 Class 3
Before pretreatment	wp≥8000pa	no test	no test	
Seams before pretreatment	wp>8000pa	wp≥8000pa	wp≥13000pa	
After every pretreatment	no test	wp>8000pa	wp≥13000pa	
Water vapour resistance	Class			Classification
	1	2	3	EN343 Class 1
R _{et} (m ² .Pa/w)	R _{et} >40	20<R _{et} ≤40	Ret≤20	

This product has been certified by Centexbel, Notified body:0493, in accordance with the EU type-examination (Module B)of PPE Regulation (EU) 2016/425.To comply with the standards: EN13688:2013; EN ISO 20471:2013/EN ISO 20471:2013+A1:2016 CLASS 3; EN343:2003+A1:2007 Class 3/1.